9-1542004 -4 Product Details

Live Product Chat US Only 8:30am - 5pm ET, Mon - Fri



9-1542004 -4
(HTS549 -U)
Active

Heat Sink Assemblies

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Heat Sink
- BGA
- Package Size = 31 [1.221] mm [in]
- For Use With BGA Semiconductor Packages
- Power Air Velocity Thermal Resistance

View all Features | Find Similar Products

Quick Links

Check Pricing & Availability
Search for Tooling
Product Feature Selector
Contact Us About This Product

Documentation & Additional Information

Product Drawings:
- 31mm HS ASSEMBLY (HTS549 -U) (PDF, English)

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

List all Documents

Additional Information:
- Product Line Information

Additional Product Images:
- Line Drawing
- Thermal Resistance Chart

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Product Type = Heat Sink
- Device Type = BGA
- For Use With = BGA Semiconductor Packages
- Finish = Black Anodize
- Material = Aluminum
- Comment = Mounting clip does not increase overall heat sink height.; Heat sink assembly includes Four Leg Clip, Part Number 1542425 -1.

Electrical Characteristics:
- Heat Sink Type = 2 Fin Radial

Termination Related Features:
- Height (mm [in]) = 9.32 [0.367]

Body Related Features:
- Package Size (mm [in]) = 31 [1.221]
- Flammability Rating = UL 94V -0

Configuration Related Features:
- Diameter (mm [in]) = 34.92 [1.375]

Industry Standards:
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:
- Brand = Tyco Electronics
- Line = ChipCoolers

Interrelated Features

When Power (W) is:	And Air Velocity is:	Thermal Resistance (°C) is:
5.0	0 LFM	13.40
5.0	200 LFM	7.80
5.0	400 LFM	4.88
5.0	600 LFM	4.28
10.0	0 LFM	11.96
10.0	200 LFM	7.30
10.0	400 LFM	4.70
10.0	600 LFM	4.04
15.0	0 LFM	10.97
15.0	200 LFM	7.23
15.0	400 LFM	4.58
15.0	600 LFM	4.04

© 2008 Tyco Electronics Corporation All Rights Reserved

Downloaded from Arrow.com.