Product Details for 55A1141 -26 -MST4 -9CS2275

55A1141 -26 -MST4 -9CS2275

Tyco Part Number: 482313 -000

Active

Spec 44 and Spec 55 Wire and Cable

RoHS Compliant (Statement of Compliance)

Product Highlights:

- Wire Source = United States
- Cable Type = Spec 55
- Cable Style = Jacketed, Round -Braid Shielded
- Wire Size (AWG/CM) = 26 AWG
- Voltage Rating = 600 VAC

View all Features

Quick Links

Check Pricing & Availability
Search for Tooling
Product Feature Selector
Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- Four Conductor Cable, Shielded, Jacketed, General Pu... (PDF, English)

Catalog Pages/Data Sheets:

- Wire and Cable,Harnessing and Protection Products (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

List all Documents

Additional Information:

- Product Line Information

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Cable Style = Jacketed, Round -Braid Shielded
- Number of Conductors = Twisted Quad

Electrical Characteristics:

- Voltage Rating (VAC) = 600

Body Related Features:

- Wire Size (AWG/CM) = 26 AWG
- Cable Jacket Color = White
- Conductor Type = Tin -Coated Copper
- Wire Color = White, White w/ Blue Stripe, White w/ Green Stripe, White w/ Orange Stripe
- Outside Diameter (mm [in]) = 2.79 [0.110]
- Wire Diameter (mm [in]) = 0.81 [0.032]
- Conductor O.D. (mm [in]) = 0.50 [0.020]

Configuration Related Features:

- Cable Type = Spec 55

Industry Standards:

- Government/Industry Qualification = Yes
- Government/Industry Part Number = M27500 -26SB4T23
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Temperature Range (°C) = -65 – +150

Operation/Application:

- Application = General Purpose - Lightweight

Packaging Related Features:

- Wire Source = United States
- Wire Size - Details = 26 AWG 0.15 mm ^{2}, 0.00024 in ^{2}, 19 x 38 AWG
- Shield (Screen) Diameter (mm [in]) = 2.41 [0.095]

Other:

- Brand = Raychem

© 2006 Tyco Electronics Corporation All Rights Reserved

Downloaded from Arrow.com.