UNIT:mm







1PC/PE BAG

PIN ASSIGNMENT

| P1 | | P2 |
|---|---|---|
| 1 | RED | 1 |
| 2 | WHITE | 2 |
| 3 | GREEN | 3 |
| 4+5 | BLACK | 4 |
| SHELL | DRAIN+BRAID | SHELL |

*Electrical test:*
*1.100% short,open,miswire test*
*2.Conduct resistance:2 Ohm(max)*
*3.Insulation resistance:10Mohm(min)*
*4.dielectric test:DC 300V*

| NO. | NAME | Q'TY | SPECIFICATION |
|---|---|---|---|
| ⑧ | TIE | 1 | BLACK L=60mm |
| ⑦ | PE BAG | 1/10 | CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"及印生产周期,有透气孔. |
| ⑥ | PE BAG | 1 | CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"及印生产周期,有透气孔. |
| ⑤ | OUT JACKET | 6g | BLACK PVC-40P (MOULD NO:WM-40) |
| ④ | OUT JACKET | 6g | BLACK PVC-40P (MOULD NO:WM-173) |
| ③ | CABLE | 1 | USB2.0 UL2725 [28AWG(7/0.12TC+AL)*1P+28AWG(7/0.12TC)*2C]+AEB(48B TC) JACKET:BLACK OD:3.5mm L=490±5mm |
| ② | CONN | 1set | USB A MALE SHELL:NICKEL PIN:G/F 3PCS TYPE INSULATOR COLOR:WHITE |
| ① | CONN | 1 | MICRO USB 5P A/M SOLDER TYPE SHELL:NICKEL PIN:G/F INSULATOR COLOR:BLACK |

CnC Tech, LLC
Industrial Cable and Connector Technology

| | | | |
|---|---|---|---|
| DRAWED | ZHONGHS | DRAWING NO | |
| CHECKED | | CUSTOMER | |
| APPROVAL | | ITEM NO. | 102-1072-BL-00050 |
| DECIDED | | DATE | 2012-02-16 |
| VERSIONS/EDITEON | A/0 | PROJECTION | |

Downloaded from Arrow.com.