

DRAWING MADE IN THIRD ANGLE PROJECTION


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

PROD 5327 CODE	LOC DF	DIST F0

P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
			E	REV & REDWN PER DF-5332 A.G.	1-7-92	DG
			F	REV PER EC DF-5470 TA	2-10-92	DG
	✓		G	REV PER 0600-1388-93 TA	5-4-94	DG







SECTION Y-Y
SCALE 8:1
(ROT.90° CW)

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± .005 ANGLES ± -	DR W. LEUFERT 5-9-89	AMP INCORPORATED Harrisburg, Pa. 17105
MATERIAL 1 2	CHK D. GUTTER 1-14-92	NAME PIN HEADER ASSEMBLY, MINI-BOX, SHROUDED, CARD EXTENDER, MILITARY
	APPD D. GUTTER 1-14-92	
	APPD T. ALEXANDER 1-17-92	
FINISH 6	PRODUCT SPEC -	SIZE C / FSCM NO 00779 / DRAWING NO 531803
	APPLICATION SPEC -	SCALE 4:1 / SHEET 1 of 2
	WEIGHT -	

AMP 1471-6 REV 3-87


CUSTOMER DRAWING

Downloaded from Arrow.com.

DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

PROD 5327 CODE	LOC	DIST	P	F	REVISIONS				
					ZONE	LTR	DESCRIPTION	DATE	APPD
						G	SEE SHEET 1 TA	-	-



RECM. .P.C. BD. LAYOUT

MILITARY PART NO.	CAVITY IDENT	G	F	E	D	C	B	A	POSN.	PART NO.
M55302/118-22	1 & 64	2.990	3.150	63	3.450	3.600	3.670	3.850	128	2-531803-2
M55302/118-21	1 & 55	2.540	2.700	54	3.000	3.150	3.220	3.400	110	2-531803-1
M55302/118-20	1 & 50	2.290	2.450	49	2.750	2.900	2.970	3.150	100	2-531803-0
M55302/118-19	1 & 45	2.040	2.200	44	2.500	2.650	2.720	2.900	90	1-531803-9
M55302/118-18	1 & 40	1.790	1.950	39	2.250	2.400	2.470	2.650	80	1-531803-8
M55302/118-17	1 & 35	1.540	1.700	34	2.000	2.150	2.220	2.400	70	1-531803-7
M55302/118-16	1 & 30	1.290	1.450	29	1.750	1.900	1.970	2.150	60	1-531803-6
M55302/118-15	1 & 25	1.040	1.200	24	1.500	1.650	1.720	1.900	50	1-531803-5
M55302/118-14	1 & 20	.790	.950	19	1.250	1.400	1.470	1.650	40	1-531803-4
M55302/118-13	1 & 15	.540	.700	14	1.000	1.150	1.220	1.400	30	1-531803-3
M55302/118-12	1 & 10	.290	.450	9	.750	.900	.970	1.150	20	1-531803-2
					SUPSD BY 2--2					1-531803-1
					SUPSD BY 2--1					1-531803-0
					SUPSD BY 2--0					531803-9
					SUPSD BY 1--9					531803-8
					SUPSD BY 1--8					531803-7
					SUPSD BY 1--7					531803-6
					SUPSD BY 1--6					531803-5
					SUPSD BY 1--5					531803-4
					SUPSD BY 1--4					531803-3
					SUPSD BY 1--3					531803-2
					SUPSD BY 1--2					531803-1

1. HOUSING MATERIAL: LIQUID CRYSTAL POLYMER PER MIL-M-24519, GLCP-30F; COLOR: GRAY.
2. CONTACT MATERIAL: BRASS.
3. END CAVITY IDENTIFICATION NUMBERS, MARKED, (SEE TABLE).
4. MUST MEET REQUIREMENTS OF MIL-C-55302.
5. EXCEPT 20 THRU 50 POSITIONS.
6. CONTACT FINISH: TABS; TIN-LEAD PLATED FOR SOLDERABILITY OVER NICKEL PER MIL-C-55302.
7. "AMP", 00779, AMP P/N, MILITARY P/N & DATE CODE, MARKED THIS APPROXIMATE AREA, FAR SIDE.
8. CAVITY NO. 1
9. .070/.054 THICK PRINTED CIRCUIT BOARD.
10. MINIMUM PAD LENGTH ON PRINTED CIRCUIT BOARD.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN INCHES
TOLERANCES ON :
2 PLC DEC ± -
3 PLC DEC ± .005
ANGLES ± -

MATERIAL 1 2

FINISH 6

DR W. LEUFERT 5-9-89
CHK D. GUTTER 1-14-92
APPD D. GUTTER 1-14-92
APPD T. ALEXANDER 1-17-92
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

AMP | AMP INCORPORATED Harrisburg, Pa. 17105

NAME
PIN HEADER ASSEMBLY, MINI-BOX, SHROUDED, CARD EXTENDER, MILITARY

SIZE	FSCM NO	DRAWING NO	
C	00779	531803	
SCALE 4:1			SHEET 2 of 2

531803

AMP 1471-6 REV 3-87

CUSTOMER DRAWING

Downloaded from Arrow.com.