



Representative photograph, actual product appearance may vary.

Due to regional agency approval requirements, some products may not be available in your area. Please contact your regional Honeywell office regarding your product of choice.

HOA0149-001

HOA Series Infrared Reflective Sensor, Transistor Output, Low profile, Plastic Package

- Features
- Phototransistor output
 - Focused for maximum response
 - Low profile housing

Description

The HOA0149 consists of an infrared emitting diode and an NPN silicon phototransistor encased side-by-side on converging optical axes in a black thermoplastic housing. The phototransistor responds to radiation from the IRED only when a reflective object passes within its field of view. The HOA0149 employs plastic molded components. For additional component information see SEP8505 and SDP8405.

Housing material is ABS. Housings are soluble in chlorinated hydrocarbons and ketones. Recommended cleaning agents are methanol and isopropanol.



HOA0149-001

HOA Series Infrared Reflective Sensor, Transistor Output, Low profile, Plastic Package


Product Specifications	
Product Type	IR Switch
On-State Collector Current	1.00 mA
Output	Transistor
Package Style	Side-Looking
Package Components	Plastic
Forward Current	40 mA
Continuous Forward Current	50 mA
Forward Voltage	1.6 V
Reverse Current	10 µA

Rise and Fall Time	15 ns
Power Dissipation	70 mW
Operating Temperature Range	-40 °C to 85 °C [-40 °F to 185 °F]
Dark Current	100 nA
Collector-Emitter Breakdown Voltage	30 V
Emitter-Collector Breakdown Voltage	5 V
Collector-Emitter Saturation Voltage	0.4 V
Availability	Global
Product Name	Reflective Sensor
Optimum Point of Response	5,08 mm [0.20 in]

Honeywell

HOA0149-001


HOA Series Infrared Reflective Sensor, Transistor Output, Low profile, Plastic Package



Honeywell

HOA0149-001

HOA Series Infrared Reflective Sensor, Transistor Output, Low profile, Plastic Package



Honeywell

HOA0149-001

HOA Series Infrared Reflective Sensor, Transistor Output, Low profile, Plastic Package

WARNING

PERSONAL INJURY

DO NOT USE these products as safety or emergency stop devices, or in any other application where failure of the product could result in personal injury.

Failure to comply with these instructions could result in death or serious injury.

WARNING

MISUSE OF DOCUMENTATION

- The information presented in this product sheet (or catalog) is for reference only. DO NOT USE this document as product installation information.
- Complete installation, operation and maintenance information is provided in the instructions supplied with each product.

Failure to comply with these instructions could result in death or serious injury.

© Copyright Honeywell Inc.1998-2004 All rights reserved.