929027-3 Product Details



Active

View 3D PDF

Timer Contacts

1.5 MM SENSOR FLATTYPE REC AG

929027-3

TE Internal Number: 929027-3

Product Highlights View All

- Timer Products Product Line
- Sensor Series
- Contact
- Wire-to-Wire
- Applies To Wire/Cable

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Documents | Features | Compliance | Additional Images

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Product Line	Timer Products
Product Type	Contact
Cable Type	FLR (Thin Walled Cable)
Wire/Cable Type	Discrete Wire
Insulation Support	With

Electrical Characteristics

Contact - Rated Current (A)	4

Termination Features

Wire/Cable Size (AWG)	17 – 20
Wire/Cable Size (mm²)	0.5 – 1
Termination Method to Wire/Cable	Crimp

Dimensions

Mating Area Interface Dimensions (mm [in])	1.50 x 0.80 [.059 x .031]

Contact Features

Contact Type	Socket
Contact Design	Spring Box Cage
Contact Base Material	CuNiSi
Contact Plating, Mating Area, Material	Silver

Configuration Features

GET 0.64 Connector System	No
Single Wire Sealing System	No

Industry Standards

RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Conditions for Usage

Applies To	Wire/Cable
Accepts Wire Insulation Diameter, Range (mm [in])	1.70 – 2.15 [0.067 – 0.0846]

Operation/Application

Application Use	Wire-to-Wire
Contact Transmits (Typical Application)	Signal

Packaging Features

Packaging Quantity	5,500
Packaging Method	Reel

Other

Series	Sensor
Brand	TE Connectivity
Node Classification	Automotive Terminals

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling

© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved

Downloaded from Arrow.com.