



## 44A1121-22-6/9-9 Product Details

[Share](#) [Print](#) [Email](#)


### Spec 44, Spec 55 and Spec RCW Wire and Cable

44A1121-22-6/9-9

**44A1121-22-6/9-9**

TE Internal Number: 3825063003

Active

[Product Highlights](#) [View All](#)

- Cable Type = Spec 44
- Wire Source = United Kingdom
- Cable Style = Jacketed, Round-Braid Shielded
- Wire Size (AWG/CM) = 22 AWG
- Voltage Rating = 600 VAC

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through  
Distributor](#)

[Documents](#) [Features](#) [Compliance](#)
**Please Note:**

Use the Product Drawing for all design activity

**Product Type Features**
**Cable Type** Spec 44

**Cable Style** Jacketed, Round-Braid Shielded

**Electrical Characteristics**
**Voltage Rating (VAC)** 600

**Dimensions**
**Conductor Outer Diameter (mm [in])** 0.79 [0.031]

**Shield (Screen) Diameter (mm [in])** 2.95 [0.116]

**Body Features**
**Wire Size (AWG/CM)** 22 AWG

**Cable Jacket Color** White

**Conductor Type** Tin-Coated Copper

**Wire Color** Blue, White

**Nominal Outside Diameter (mm [in])** 3.35 [0.132]

**Wire Diameter (mm [in])** 1.19 [0.0468]

**Configuration Features**
**Number of Conductors** Twisted Pair

**Industry Standards**
**Government/Industry Qualification** No

**RoHS/ELV Compliance** RoHS compliant, ELV compliant

**Lead Free Solder Processes** Not relevant for lead free process

**RoHS/ELV Compliance History** Always was RoHS compliant

**Conditions for Usage**
**Temperature Range (°C)** -65 - +150

**Wire Size - Details** 22 AWG 0.38 mm<sup>2</sup>, 0.00059 in<sup>2</sup>, 19 x 34 AWG

**Operation/Application**
**Application** General Purpose - Light Weight

**Packaging Features**
**Wire Source** United Kingdom

**Other**
**Brand** Raychem

**Node Classification** Twisted Pair Cable

**Related Products**

Not quite the product you're looking for?

[Find Similar Products](#)
[View Part in Product Feature Selector](#)
[Check for Tooling](#)
[Feedback](#)
**Corporate Information**
[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms of Use of TE.com](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)
**Quick Links**
[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)
[Terms & Conditions of Sale](#)
**Customer Support**
[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)
**Keep Me Informed**
