**Part Number :** 936014683
**Product Description :** Heavy-Duty Standard (STD) Single Lever Hood, Polyamide, with 2 Pegs, Side Entry, with Cable Gland, Size «32x13», Pg21 Thread, Black
**Series Number :** 93601
**Status :** Active
**Product Category :** Heavy-Duty Connectors
**Engineering Part Number :** 7908.6643.1



## Documents and Resources

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Relevant |
| EU ELV | Compliant per 2000/53/EC |
| Low-Halogen Status | Not Relevant |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

Downloaded from Arrow.com.

UKCA - Declaration of Conformity

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Heavy Duty Connectors |
| Series | 93601 |
| Description | Heavy-Duty Standard (STD) Single Lever Hood, Polyamide, with 2 Pegs, Side Entry, with Cable Gland, Size «32x13», Pg21 Thread, Black |
| Component Type | Single Lever Hood |
| IP Rating | IP66, IP67 |
| Product Name | Heavy-Duty Connectors |
| Standard | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Type | STD |
| UPC | 887191842394 |

### Agency

| | |
|---|---|
| CSA | 256883 |
| UL | E249674 |

### Electrical

| | |
|---|---|
| Voltage - Maximum | 500V |

### Physical

| | |
|---|---|
| Cable Diameter | 11.00-18.00mm |
| Component Size | «32X13» |
| Entry Location | Side |
| Gland Color | Black RAL 9005 |
| Hood Color | Black RAL 9005 |
| Lock to Mating Part | Yes |
| Material - Cable Gland | Polyamide |
| Material - Hood | Polyamide |

Downloaded from Arrow.com.

| | |
|---|---|
| Material - Peg | Polyamide |
| Net Weight | 39.000/g |
| Number of Pegs | 2 |
| Packaging Type | Bag |
| Thread Size | Pg21 |
| Thread Type | (Pg) |

## Mates With / Use With

### Use with Part(s)

| Description | Part Number |
|---|---|
| Use With | Size «32x13» S-QD Inserts |



Downloaded from Arrow.com.