Data Sheet | Item Number: 727-206

4-level end plate; marking: a-b-c-d--d-c-b-a; 7.62 mm thick; orange

https://www.wago.com/727-206



Color: orange

Physical data	
Width	7.62 mm / 0.3 inches
Height	126 mm / 4.961 inches
Depth	44.3 mm / 1.744 inches

Mechanical data	
Marking	a-b-c-d--d-c-b-a

Material data	
Note (material data)	Information on material specifications can be found here
Color	orange
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.381 MJ
Weight	14.4 g

Environmental requirements	
Processing temperature	-35 … +85 °C
Continuous operating temperature	-60 … +105 °C

Commercial data	
Product Group	12 (Matrix Patch Board)
PU (SPU)	25 pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332233552
Customs tariff number	85389099990

Downloaded from Arrow.com.

Product Classification

UNSPSC	39121702
eCl@ss 10.0	27-14-11-33
eCl@ss 9.0	27-14-11-33
ETIM 9.0	EC000886
ETIM 10.0	EC000886
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 727-206

Documentation

Bid Text

727-206	19.02.2019	xml 2.55 KB	
727-206	18.08.2017	doc 23.50 KB	

CAD/CAE-Data

CAD data

2D/3D Models 727-206

CAE data

EPLAN Data Portal 727-206

WSCAD Universe 727-206

ZUKEN Portal 727-206

Downloaded from Arrow.com.

1 Compatible Products

1.1 Optional Accessories

1.1.1 Tool

1.1.1.1 Operating tool



Item No.: 210-719
Operating tool; Blade: 2.5 x 0.4 mm; with a partially insulated shaft



Item No.: 210-647
Operating tool; Blade: 2.5 x 0.4 mm; with a partially insulated shaft; multicoloured

Downloaded from Arrow.com.