© – TE Connectivity. All Rights Reserved.

| REVISIONS | | | | | |
|---|---|---|---|---|---|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| | E1 | TABLE DIMENSIONS UPDATED | 15APR2026 | GSK | AK |







| Product Size | 2.4 | 3.2 | 4.8 | 6.4 | 9.5 | 12.7 | 19.0 | 25.4 | 38.1 | 50.8 | 60.0 |
|---|---|---|---|---|---|---|---|---|---|---|---|
| Minimum Supplied I.D. | 2.38 (.094) | 3.18 (.135) | 4.75 (.187) | 6.35 (.250) | 9.53 (.375) | 12.70 (.500) | 19.05 (.750) | 25.40 (1.000) | 38.10 (1.500) | 50.80 (2.000) | 57.15 (2.250) |
| Maximum Recovered I.D. | 0.79 (.031) | 1.07 (.042) | 1.57 (.062) | 2.11 (.083) | 3.18 (.125) | 4.22 (.166) | 6.35 (.250) | 8.46 (.333) | 19.05 (.750) | 25.40 (1.00) | 19.05 (.750) |
| Recovered Wall Thickness ±0.08 (.003) | 0.58 (.023) | 0.58 (.023) | 0.58 (.023) | 0.58 (.023) | 0.61 (.024) | 0.61 (.024) | 0.61 (.024) | 0.64 (.025) | 0.51 (.020) | 0.64 (.025) | 0.76 (.030) |
| Minimum Sleeve Flattened Width | 4.45 (.175) | 5.84 (.230) | 8.00 (.315) | 10.7 (.420) | 15.5 (.610) | 20.4 (.803) | 30.5 (1.20) | 40.4 (1.59) | 60.3 (2.37) | 80.0 (3.15) | 88.9 (3.50) |

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS (inches).

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL: CROSSLINKED POLYOLEFIN

FINISH: –

DWN AFK 12OCT2018
CHK – –
APVD LS 15OCT2018
PRODUCT SPEC RW–2511
APPLICATION SPEC —
WEIGHT

TE Connectivity

NAME: TTMS PRODUCT – –

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A3 | – | C–MCD170000 | — |

CUSTOMER DRAWING

SCALE 1:1 SHEET 1 OF 1 REV E1



Downloaded from Arrow.com.