

Part Number : 16020087
Product Description : SL Crimp Terminal, Series 70058, Female, 24-22 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Reel
Series Number : 70058
Status : Active
Product Category : Crimp Terminals
Engineering Part Number : 70058-0024
Packaging Alternative : 16020103 (Bag)

Documents and Resources

Drawings

016020087_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-70058-001.pdf

PS-70400-001.pdf

TS-70058-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	70058
Description	SL Crimp Terminal, Series 70058, Female, 24-22 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Reel
Application	Wire-to-Board, Wire-to-Wire
Product Name	CyClone,SL
UPC	800753596023

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.120/g
Packaging Type	Reel
Plating min - Mating	0.380µm
Plating min - Termination	2.000µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.63mm max.
Wire Size (AWG)	22, 24

Downloaded from Arrow.com.

Wire Size mm^2	N/A

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
SL Single Row Crimp Housings and CPA Retainers	70066
SL Dual Row Crimp Housings	70450

Application Tooling

Global

Description	Part Number
Insertion Tool for 70021,70028, 70110, 71851 Terminals / Extraction Tool for 91821 Terminals	11020022
PremiumGrade Hand Crimp Tool for SL Crimp Terminals, 24-22 AWG and 36-32 AWG	638118700
FineAdjust Applicator for SL Crimp Terminals, for 24-22 AWG Wire with Insulation Diameter 1.40-1.63mm	639023200
T2 Terminator for Female Crimp Terminal	639123200

Downloaded from Arrow.com.