PRODUCT FAMILIES

- Pin Headers and Sockets
- Clips and Insulators
- Banana Plugs and Jacks
- Grabbers, Probes and Spade Terminals
- Test Leads and Patch Cords
  - Plunger Test Leads
  - Banana Plug Test Leads
  - Alligator Clip Patch Cords
- Coaxial Cable Assemblies
- DMM Kits

ISO 9001:2000

Alligator Clip Patch Cords

Insulated Mini-Alligator Lead Set

Model # BU-00285

- Material: Clip: nickel-plated steel with PVC insulators; Hook-up Wire: #22 (19/34) AWG copper with 105°C PVC insulation
- Length: 18", (.46m)
- Colors: Includes 2 each: Black, Red, Yellow, Green, White
- Rating: Hands free testing at 300V, 5 Amp

TOOL SEARCH TOOLS
MUELLER OR DISTRIBUTOR STOCK SEARCH
PART #
SEARCH
TOOL CROSS COMPETITOR PART #
Choose a Brand
PART #
SEARCH
TOOL MaterMate® DMM ACCESSORY SELECTOR
Select Meter Make
Select a Make First
TOOL BUILD A PCB HEADER OR SOCKET
OVER 10,000 IN STOCK!
GO

Insulated Alligator Lead Set

Model # BU-00286

- Material: Clip: nickel-plated steel with PVC insulators; Hook-up Wire: #22 (19/34) AWG copper with 105°C PVC insulation
- Length: 12" (.3m)
- Colors: Includes 1 each: Black, Red, Yellow, Green, White
- Rating: Hands free testing at 300V, 7 Amp

Insulated Alligator Lead Set

Model # BU-00287

- Material: Clip: nickel-plated steel with PVC insulators; Hook-up Wire: #22 (19/34) AWG copper with 105°C PVC insulation
- Length: 18" (.46m)
- Colors: Includes 2 each: Black, Red, Yellow, Green, White
- Rating: Hands free testing at 300V, 7 Amp

Insulated Alligator Clips on Both Ends

Model # BU-3030-A-**-*

- Material: Alligator Clip: nickel-plated steel with PVC insulator; Hook-up Wire: #20 (41/36) AWG tinned copper with 105°C PVC insulation
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- *Std. Colors: -0 Black, -2 Red
- Rating: Hands free testing at 300V, 10 Amps

Insulated Alligator Clips on Both Ends - Coiled Cord

Model # BU-3030-C-24-*

- Material: Clip: nickel-plated steel alligator with insulator (BU-60 and BU-62-*); Coiled Cord: single conductor 18AWG wire with 4mm O.D.
- 24" (.6m) retracted, 120" (3.) extended
- *Std. Colors: -0 Black, -2 Red
- Rating: Hands free testing at 300V, 15 Amps

Insulated Alligator Clip to Stackable Dual Banana Plug with RG58

Model # BU-3070-C-**-0

- Material: Alligator Clip: nickel-plated steel with PVC insulator; Double Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring; Coaxial Cable: Shielded RG58C/U, MIL-C-17F, 50 ohm
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- Rating: Hands free testing at 300 VRMS

Insulated Mini-Alligator Clip on Both Ends

Model # BU-3131-A-**-*

- Material: Alligator Clip: nickel-plated steel with PVC insulator; Hook-up Wire: #20 (41/36) AWG tinned copper with 105°C PVC insulation
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- *Std. Colors: -0 Black, -2 Red
- Rating: Hands free testing at 300 VAC, 5 Amps

Shrouded Banana Plug to Piercing Clip - Silicone



Model # JP-7505-83-**-*

- Piercing clips are J.S. Popper brand
- Material: Piercing Clip: JP-8783; Banana Plugs: nickel-plated brass body, nickel-plated beryllium copper spring; Hook-up Wire: #18 AWG, silicone insulator
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m)
- *Std. Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue
- Rating: 300V, 3 Amp

Ultra-Flex Test Lead Wires

Model # WI-M-18-*

- Material: Wire: #18 AWG, silicone
- *Std. Colors: -0 Black, -2 Red,-4 Yellow, -5 Green, -6 Blue, -9 White
- Rating: 3kV, 22 Amp

Downloaded from AllPart.com