

[CONNECTORS](#)

RF CONNECTORS



✓ Active

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

> [See All Documentation](#)

TE CONNECTIVITY (TE)

BNC Str Jk Hex 50Ohm Nickel Pltd RG58C/U

Miniature Coax | STA , U

1-1337441-0
TE Internal Number: 1-1337441-0

EU RoHS Compliant with Exemptions
EU ELV Compliant with Exemptions

Connector Interface **BNC**

Connector Style **Jack**

Mated Outer Diameter (Approximate) **14.529 mm [.572 in]**

Impedance (Ω) **50**

Cable Type **Raychem 5021D1331, Raychem 5021D1831, Raychem 5021M1631, Raychem EPD 71169Q, RG 141A, RG 58C, URM 43, URM 76**

> [See All Features](#)

North America ▾

Inventory does exist through Waldom (TE's master distributor) but is only available for purchase through a TE authorized distributor. Please contact your preferred authorized distributor for purchasing options.

FIND AUTHORIZED DISTRIBUTORS >

GET SAMPLE	
SAVE TO LIST ▾	
CHECK FOR TOOLING	
FIND SIMILAR PRODUCTS	

DOCUMENTATION

FEATURES

PRODUCT COMPLIANCE

Product Drawings

BNC STRAIGHT JACK CRIMP 50 OHM RG58C/U, 141A/U, URM43, 76, KX15
 PDF **(TIFF AVAILABLE)**
English

CAD Files

3D PDF
 PDF
3D
 Customer View Model
 2D_DXF.ZIP
English

Customer View Model
 3D_IGS.ZIP
English

Customer View Model



Compatible Products

> [Contact Product Support](#)

Also in the Series | [STA](#)



Board-to-Board Headers & Receptacles (10)



Data Bus Connectors (2)



Data Bus Couplers (10)



Data Bus Terminators (32)

Also in the Series | [U](#)



Rectangular Connector Hardware (1)



RF Connectors (70)



SO DIMM Sockets (2)

Customers Also Bought

RF CONNECTORS



N Str Plg Hex 50Ohm
Silver Pltd PSF 1/4M
1-1337410-0

HEAT SHRINK TUBING



ATUM-32/8-0-STK
ATUM-32/8-0-STK

IN-SERIES ADAPTERS



BNC Ins BH Adp JJ
50Ohm Nickel Pltd
1-1337454-0

RF CONNECTORS



BNC RM BHJ Hex 50Ohm
Nickel Pltd RG58C/U
1-1337433-0

[About TE Connectivity](#)

[For Partners](#)

[Customer Support](#)

[CALL US](#)

[LIVE CHAT](#)

[United States](#)