

© 2021 TE Connectivity. All Rights Reserved.

printed on 5 Feb 2024 13:46 (China Standard Time) from TE460523


2391298-1




2391298-2




2391298-3





2391298-4





PLUG SHOWN WITH SECONDARY LOCK IN CLOSE POSITION (NOT THE DELIVERY CONDITION)

















2391298-1 AS SHOWN

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	PRELIMINARY	06JUL21	KZ	JZ
	A	RELEASED	08APR22	KZ	JZ
	A1	ECN-24-250960	05FEB24	K.Z	J.Z

NOTES:
1.DELIVERY CONDITION:TPA IN PRE-LOCK POSITION.IF TPA UNECPECTED BECOME ENGAED , PLEASE MOVE TPA TO PRE-LOCK POSITION.
2.MATING PART TE P/N : X-2386152-X
3.CONNECTOR VALIDATED TO LV214
4.APPLICABLE TERMINAL P/N : X-1703930-X

PART NO	REV	CODING	COLOR	MATERIAL NO
2391298-4	A	D	GREEN	PA66
2391298-3	A	C	BLUE	PA66
2391298-2	A	B	GREY	PA66
2391298-1	A	A	BLACK	PA66

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3
0 PLC ±-
1 PLC ±0.1
2 PLC ±0.01
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±-

MATERIAL: SEE TABLE -

FINISH: -

DWN K.ZHOU 06JUL21
CHK T.DONG 06JUL21
APVD J.ZONG 06JUL21
PRODUCT SPEC 108-160392
APPLICATION SPEC 114-160496
WEIGHT -

TE Connectivity

NAME 28POS NANOMQS , REC HSG CABLE VERSION -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2391298	-

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 2 | REV A1


Downloaded from Arrow.com.

© 2021 TE Connectivity. All Rights Reserved.


Printed on 5 Feb 2024 13:46 (China Standard Time) from TE46052

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			


1-2391298-1




1-2391298-2




1-2391298-3





1-2391298-4





PLUG SHOWN WITH SECONDARY LOCK IN CLOSE POSITION (NOT THE DELIVERY CONDITION)
















1-2391298-1 AS SHOWN



NOTES:
1.DELIVERY CONDITION:TPA IN PRE-LOCK POSITION.IF TPA UNECPECTED BECOME ENGAED , PLEASE MOVE TPA TO PRE-LOCK POSITION.
2.MATING PART TE P/N : X-2386152-X
3.CONNECTOR VALIDATED TO LV214
4.APPLICABLE TERMINAL P/N : X-2291853-X

FPC SPEC



ITEM	6PIN	16PIN
DIM.A	12.2	32.2

PART NO	REV	CODING	COLOR	MATERIAL NO
1-2391298-4	A	D	GREEN	PA66
1-2391298-3	A	C	BLUE	PA66
1-2391298-2	A	B	GREY	PA66
1-2391298-1	A	A	BLACK	PA66

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3
0 PLC ±-
1 PLC ±0.1
2 PLC ±0.01
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±-

MATERIAL SEE TABLE -

FINISH - -

DWN K.ZHOU 06JUL21
CHK T.DONG 06JUL21
APVD J.ZONG 06JUL21
PRODUCT SPEC 108-160392
APPLICATION SPEC 114-160496
WEIGHT -

TE Connectivity

NAME 28POS NANOMQS , REC HSG FPC VERSION -

SIZE A3 | CAGE CODE 00779 | DRAWING NO C-2391298 | RESTRICTED TO -

CUSTOMER DRAWING | SCALE 2:1 | SHEET 2 OF 2 | REV A1

1470-19 (3/13)

Downloaded from Arrow.com.