D SUB IP 67 FE ANG_PCB_15P_S4_METAL FRAM

Spotted an error? | Print page | Back

Image is for illustration purposes only. Please refer to product description.

Accessories

Login to MyHARTING for pricing and stock check

Quantity: 25

Shopping cart

Email inquiry

Catalogue
HARTING Device Connectivity - Page 378

Browse

Download

- Features
- Connection data
- Dimensions and weight
- Supplementals

Part number:	09 67 615 6758
Description:	D SUB IP 67 FE ANG_PCB_15P_S4_METAL FRAM

Features

Application:	Board Connector Panel Mount
Class of Protection:	IP67
Contact Pitch:	2.54 mm
Gender:	Turned Female Contact
Mating Hardware:	Flange Thread 4-40
No. of contacts:	15
Performance level:	S4
RoHS conformity:	Yes
Termination Type:	Solder
Type:	Rear Mount Angled Metal Frame

Top

Connection data

Current:	5 A @ 20°C

Top

Dimensions and weight

Net Weight:	25 g

Top

Supplementals

Series:	D-Sub Waterproof

Top

Downloads

Title	Download
CAD data 3D	STEP
CAD data 3D	JT
HARTING Device Connectivity - Page 378	PDF

Accessories

Image	Part number	Description	Tech. info	Quantity
	09 67 002 9051	D SUB IP 67 SHIELDED CAP_MA_15p_4-40 UNC		1 Shopping cart
	09 67 002 9056	D SUB IP 67 SHIELDED CAP_MA_15p_M3		1 Shopping cart
	09 67 002 9007	FEMALE SCREW LOCK 4-40 UNC		1 Shopping cart

Recently viewed - Delete

D SUB IP 67 MA STR_PCB_9P_S4_METAL FRAME
Show product details

D SUB IP 67 MA ANG_PCB_09P_S4_METAL FRAM
Show product details

D SUB IP 67 FE STR_PCB_9P_S4_METAL FRAME
Show product details

D SUB IP 67 FE ANG_PCB_09P_S4_METAL FRAM
Show product details

D SUB IP 67 MA STR_PCB_9P_S4_METAL FRAME
Show product details

D SUB IP 67 MA ANG_PCB_9P_S4_METAL FRAME
Show product details

D SUB IP 67 FE STR_PCB_9P_S4_METAL FRAME
Show product details

D SUB IP 67 FE ANG_PCB_9P_S4_METAL FRAME
Show product details

DSUB SV FE SSDP ANG87-254 50P AU2
Show product details

DSUB SV MA SSDP STR 50P AU3
Show product details

Recently searched

No searches have been done yet.

Downloaded from Arrow.com.