



BNC RA Pl to SMB RA Pl RG-174 50 Ohm 1 M

095-850-238M100

Find In Stock & Buy Now

RF Cable Assembly BNC Right Angle Plug to SMB Right Angle Plug RG-174 1 M Length 50 Ohms

+ Add To Parts List ≡ Add To Compare

Product Compliance

- RoHS (EU). Compliant with Exemption 6C - [View Certificate](#)
- California residents see [Prop 65 Warning](#)
- Additional compliance information is available in our [Compliance Center](#).

Description

RF Cable Assembly BNC Right Angle Plug to SMB Right Angle Plug RG-174 1 M Length 50 Ohms

Downloads

095-850-237-XXX Customer Drawing (Size: 222 kb)

Product Life Cycle

Part Status	Active
-------------	--------

Product Specifications

Cable Length	39.37 in (1000 mm)
Cable Type	RG-174
Connector 1 Part Number	112178
Connector 1 Series	BNC
Connector 1 Style	R/A Plug
Connector 2 Part Number	142194
Connector 2 Series	SMB
Connector 2 Style	R/A Plug
Export Control Classification Number	EAR99
Impedance (Ohms)	50
Low PIM	No
Mil Qualified	No

You May Also Be Interested In

BNC RA Pl to SMB Str Pl RG-174 50 Ohm 12 in
095-850-237-012

BNC RA Pl to SMB RA Pl RG-174 50 Ohm 6 in
095-850-238-006

BNC Str Pl to SMB RA Pl RG-174 50 Ohm 24 in
245103-02-24.00

BNC RA Pl to SMB RA Pl RG-174 50 Ohm 18 in
095-850-238-018

BNC RA Pl to SMB RA Pl RG-174 50 Ohm 500 mm
095-850-238M050

Need A Custom RF Cable Assembly?

Build Your Cable Now

Feedback

Subscribe And Stay Connected With Amphenol RF

Enter Email Address

Submit

By submitting your email, you are agreeing to receive occasional updates from Amphenol RF.

This site is protected by reCAPTCHA and the Google Privacy Policy and Terms of Service apply.

Company

- About Us
- Locations
- Careers
- Newsroom
- Capabilities
- Quality

Quick Links

- Distributor Inventory
- Competitor Cross Reference
- Compliance Center
- Document Library
- Quickbuild RF
- Anti-Slavery/Human Trafficking

Support

- Contact Us
- Local Representative Locator
- Authorized Distributors

Account

- Login / Sign Up
- My Parts List
- Extranet Login

Follow Us

