THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA. MIN. in (mm)	BUNDLE DIA. MAX. in (mm)	A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs./100 pcs. (g)
BT1M	.06 (1.5)	0.90 (23)	.036 (0.9)	.095 (2.4)	.110 (2.8)	.156 (4.0)	.172 (4.4)	4.0 (102)	18 (80)	MINIATURE	.05 (22)
BT1.5M	.06 (1.5)	1.5 (38)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	6.3 (160)	18 (80)	MINIATURE	.09 (43)
BT2M	.06 (1.5)	2.0 (51)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	7.9 (201)	18 (80)	MINIATURE	.12 (53)
BT4M	.06 (1.5)	4.00 (102)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	14.2 (361)	18 (80)	MINIATURE	.21 (93)

NOTES:
1. SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
11A	7-1-25	KEMA	MPH	DJSL	CHANGED MATERIAL BLOCK TO NYLON 6.6 WITH 316 STAINLESS STEEL BARB	017076/00
10	5-2-06	JABO	JVL		REMOVED STRAIGHT TIP REFERENCE & TP STYLE COLUMN	0037

TITLE

DOME-TOP Barb Ty CABLE TIES BT SERIES

CUSTOMER DRAWING

ITEM REVISION NAME: BT_0037_SH1/AB

DATASET FILE NAME: BT-0037_DC_SH1 of 3 r11A

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]
.X ± .10 [2.5] .XXX ± .020 [.51]
.XX ± .02 [.5] ANGLES ± -
THIRD ANGLE PROJECTION

MATERIAL: NYLON 6.6 WITH 316 STAINLESS STEEL BARB

DRAWING NUMBER: BT-0037

DRAWN BY	DATE	CHK	SCALE	SIZE
PMH	6-24-93	JVL	NONE	A

SHT 1 OF 3

NXGLOBAL_ASIZE

Downloaded from Arrow.com.