Data Sheet | Item Number: 756-3206/140-100

M16 cable; M16 socket; angled; 14-pole; Length: 10 m

https://www.wago.com/756-3206/140-100


DISCONTINUED:
01.01.2027




Pin A, L: 0.75 mm²
Pin C - J, N - T: 0.34 mm²

A	brown	N	pink-brown
C	white-pink	O	violet
E	black	P	white
G	pink	R	red
J	green	S	gray
L	blue	T	yellow
M	commoned with A	U	commoned with L

Color: ■ black





Dimensions in mm

Technical data	
Connection type	M16 socket - free end
Pole number	14
Cable connection direction to mating direction	90 °
Cable length	10 m
Operating voltage	150 V
Operating current	4 A
Operating current	6 mm² 0,75 A
Rated impulse withstand voltage	1.2 kV

Downloaded from Arrow.com.

Mechanical data

Bending cycles	2 million
Drag chain capability	Yes
Weight	971 g
Color	black

Environmental requirements

Ambient (operating) temperature (dynamic)	-30 … +90 °C
Ambient (operating) temperature (static)	-40 … +90 °C
Protection type	IP67

Commercial data

PU (SPU)	1 pcs
Packaging type	unpacked
Country of origin	DE
GTIN	4066966515404
Customs tariff number	85444290900
End of Sale	2027-01-01
End of Production	2027-01-02
End of Delivery	2027-03-01
End of Service and Repair	2027-07-01

Product Classification

UNSPSC	26121629
eCl@ss 10.0	27-06-03-11
eCl@ss 9.0	27-06-03-11
ETIM 9.0	EC001855
ETIM 10.0	EC001855
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant,No Exemption

Approvals / Certificates

Declarations of conformity and manufacturer's declarations

Approval	Standard	Certificate Name
EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
UK-Declaration of Conformity WAGO GmbH & Co. KG	-	-

Downloaded from Arrow.com.

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 756-3206/140-100

Documentation

System Description

Sensor/Actuator Boxes – General Product Information	pdf 428.34 KB	

CAD/CAE-Data

CAE data

WSCAD Universe 756-3206/140-100

Downloaded from Arrow.com.