

1857008-1

TE Internal Number: 1857008-1

Active

View 3D PDF

2mm Hard Metric PCB Mount Connectors (Z-PACK 2mm HM)

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

Connector

Connector Assembly

Connector Style = Plug

Type = Type C

Interface Type = 2mm HM

View all Features

Quick Links

Pricing & Availability

Search for Tooling

Product Feature Selector

Contact Us About This Product

Add to My Part List

Request Sample

Find Similar Products

Buy Product

Documentation & Additional Information	
<div><div>Product Drawings:</div><div><div>Z-PACK 2mm HM TYPE C 55 POS. RIGHT ANGLE MALE CONNE... (PDF, English)</div></div><div><div>Catalog Pages/Data Sheets:</div><div><div>None Available</div></div></div><div><div>Product Specifications:</div><div><div>None Available</div></div></div><div><div>Application Specifications:</div><div><div>Z-PACK 2mm HM Interconnection System for Board-to-Bo... (PDF, English)</div></div></div><div><div>Instruction Sheets:</div><div><div>None Available</div></div></div><div><div>CAD Files: (CAD Format & Compression Information)</div><div><div>2D Drawing (DXF, Version A)</div><div>3D Model (IGES, Version A)</div><div>3D Model (STEP, Version A)</div></div></div></div> <div><div>Additional Information:</div><div><div>Product Line Information</div></div><div><div>Related Products:</div><div><div>Tooling</div></div></div></div>	<div>List all Documents</div>

Product Features (Please use the Product Drawing for all design activity)	
<div><div>Product Type Features:</div><div><div>Product Type = Connector</div><div>Connector Type = Connector Assembly</div><div>PCB Mounting Orientation = Right Angle</div></div><div><div>Mechanical Attachment:</div><div><div>Board Mount = Free Board</div></div></div><div><div>Termination Features:</div><div><div>Interface Type = 2mm HM</div><div>Termination End Plating = Tin over Nickel</div></div></div><div><div>Dimensions:</div><div><div>Module Length (mm [in]) = 24.90 [0.980]</div></div></div><div><div>Body Features:</div><div><div>Type = Type C</div></div></div><div><div>Contact Features:</div><div><div>Contact Configuration = ACTION PIN Post</div><div>Feedthrough Post Length (mm [in]) = 3.80 [0.150]</div><div>CompactPCI = No</div><div>Contact Plating, Mating Area, Material = Performance Based</div><div>Grounding Contact = Without</div><div>Contact Style = Short Tail</div><div>Contact Mating Area Length (mm [in]) = 8.20 [0.323]</div><div>Contact Base Material = Phosphor Bronze</div></div></div></div>	<div><div>Housing Features:</div><div><div>Connector Style = Plug</div><div>Mating Alignment = Without</div><div>Housing Color = Gray</div><div>Housing Material = Polyester - GF</div></div><div><div>Configuration Features:</div><div><div>Number of Rows = 11</div><div>Number of Positions = 55</div><div>Shielded = No</div></div><div><div>Industry Standards:</div><div><div>RoHS/ELV Compliance = RoHS compliant, ELV compliant</div><div>Lead Free Solder Processes = Not relevant for lead free process</div><div>RoHS/ELV Compliance History = Always was RoHS compliant</div><div>UL Flammability Rating = UL 94V-0</div></div><div><div>Other:</div><div><div>Brand = TE Connectivity</div></div></div></div></div></div>

Corporate Information

About TE

Investors

News Room

Supplier Portal

Careers

Terms & Conditions

Privacy Policy

Global Accessibility Statement

Quick Links

Distributor Inventory

Product Cross Reference

Documents & Drawings

Product Compliance Support Center

Site Map

Customer Support


Email or Chat With Us


Find a Phone Number


Knowledge Base


Manage Your Account


Keep Me Informed

















© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved | [Provide Website Feedback](#)

Downloaded from [Arrow.com](#)