

# WOUV-240DC Product Details

[Share](#) | [Print](#) | [Email](#)


✓ Active

## Sensors & Protective Relays

WOUV-240DC=RELAY, OVER/UNDERVOLTAGE

**WOUV-240DC** (4-1618107-6)

TE Internal Number: 4-1618107-6

### Product Highlights [View All](#)

- Relay Type = Protective Relay
- WOUV Series
- Operate/Set Voltage = 264 V
- Release/Reset Voltage = 108 V
- DC Actuating System

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

[Documents](#) | [Features](#) | [Compliance](#)

**Please Note:**  
Use the Product Drawing for all design activity

Product Type Features		Configuration Features	
Relay Type <sup>?</sup>	Protective Relay	Contact - Arrangement <sup>?</sup>	1 Form A, SPST-NO, 1 N/O
<b>Mechanical Attachment</b>		Contact Arrangement, Additional Output <sup>?</sup>	1 Form B, SPST-NC, 1 N/C
Mounting Options	Flange Mount	<b>Industry Standards</b>	
<b>Electrical Characteristics</b>		RoHS/ELV Compliance <sup>?</sup>	Not ELV/RoHS compliant
Operate/Set Voltage (V) <sup>?</sup>	264	Lead Free Solder Processes <sup>?</sup>	Not relevant for lead free process
Release/Reset Voltage (V) <sup>?</sup>	108	<b>Conditions for Usage</b>	
Actuating System <sup>?</sup>	DC	Temperature Range (°C)	-40 - +75
Input Voltage (VDC)	12 - 560	<b>Operation/Application</b>	
Phase <sup>?</sup>	Single	Protection Function <sup>?</sup>	Over/Undervoltage
Contact Rating	5A Resistive @ 28 VDC/120VAC	Time Delay <sup>?</sup>	With
<b>Termination Features</b>		<b>Other</b>	
Termination Type	Screw Terminal	Series <sup>?</sup>	WOUV
<b>Dimensions</b>		Brand	Kilovac
Approx. Dimensions (L x W x H) (mm [in])	88.9 x 76.2 x 50.8 [3.5 x 3.0 x 2.0]	Node Classification	Protective Relays

**Related Products**

Not quite the product you're looking for?  
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

### Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms of Use of TE.com](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

### Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)
- [Terms & Conditions of Sale](#)

### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

### Keep Me Informed

