

# Female test connector - PSB 4/7/6



0303299

<https://www.phoenixcontact.com/us/products/0303299>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

---



Female test connector, color: silver

---

## Your advantages

- Test sockets PSB ... are used for a reliable test connection
- All test sockets are screwed into the bridge shaft
- All test sockets are screwed into the bridge shaft

# Female test connector - PSB 4/7/6



0303299

<https://www.phoenixcontact.com/us/products/0303299>

## Commercial Data

Item number	0303299
Packing unit	1 pc
Minimum order quantity	10 pc
Sales Key	B01
Product Key	BE1Z3X
Catalog Page	Page 590 (C-1-2019)
GTIN	4017918000417
Weight per Piece (including packing)	2.17 g
Weight per Piece (excluding packing)	2.17 g
Customs tariff number	85366990
Country of origin	PL

# Female test connector - PSB 4/7/6

0303299

<https://www.phoenixcontact.com/us/products/0303299>



## Technical Data

### Product properties

Product type	Test socket
Number of positions	1

### Dimensions

Dimensional drawing	
Width	6 mm
Length	6 mm
Pin diameter	4.1 mm

### Material specifications

Color	silver
Contact material	Silver-plated brass

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------


# Female test connector - PSB 4/7/6

0303299

<https://www.phoenixcontact.com/us/products/0303299>



## Drawings



# Female test connector - PSB 4/7/6



0303299

<https://www.phoenixcontact.com/us/products/0303299>

## Classifications

### ECLASS

ECLASS-9.0	27440313
ECLASS-10.0.1	27440313
ECLASS-11.0	27440313

### ETIM

ETIM 8.0	EC002255
----------	----------

### UNSPSC

UNSPSC 21.0	20122000
-------------	----------

# Female test connector - PSB 4/7/6



0303299  
<https://www.phoenixcontact.com/us/products/0303299>

## Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2022 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)