




**Part Number :** [150310261](#)  
**Product Description :** 0.30mm Pitch Premo-Flex FFC  
Jumper with Notches, Same Side Contacts (Type A),  
51.00mm Cable Length, Gold (Au) Plating, 61 Circuits  
**Series Number :** 15031  
**Status :** Active  
**Product Category :** Flat-Flexible Cable (FFC)



## Documents and Resources

### Drawings

- [150310261 sd.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

### Specifications

- [150310001-000.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                                         |
|--------------------|---------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                                            |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                            |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                                          |
| REACH SVHC         | Not Contained per D(2023)3788-DC (14 Jun 2023)                                                          |
| EU RoHS            | Compliant per EU 2015/863                                                                               |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

|              |                                                                                                                                    |
|--------------|------------------------------------------------------------------------------------------------------------------------------------|
| Status       | Active                                                                                                                             |
| Category     | Flat-Flexible Cable (FFC)                                                                                                          |
| Series       | 15031                                                                                                                              |
| Description  | 0.30mm Pitch Premo-Flex FFC Jumper with Notches, Same Side Contacts (Type A), 51.00mm Cable Length, Gold (Au) Plating, 61 Circuits |
| Product Name | Premo-Flex FFC Jumper                                                                                                              |
| UPC          | 195842786653                                                                                                                       |

### Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 0.2A |
| Voltage - Maximum             | N/A  |

### Physical

|                               |                                     |
|-------------------------------|-------------------------------------|
| Cable Length                  | 51.00mm                             |
| Circuits (Loaded)             | 61                                  |
| Contact Layout Type           | A (same side)                       |
| Design Feature                | Miniaturization, Superior Retention |
| Material - Plating Mating     | Gold                                |
| Net Weight                    | 0.227/g                             |
| Packaging Type                | Bag                                 |
| Pitch - Mating Interface      | 0.30mm                              |
| Temperature Range - Operating | -40° to +105°C                      |

|                   |                           |
|-------------------|---------------------------|
| Termination Style | FFC Connector             |
| Wire/Cable Type   | Flat Flexible Cable (FFC) |
| Wire Size (AWG)   | N/A                       |

---

## Mates With / Use With

### Mates with Part(s)

| Description                                                                                                                                               | Part Number       |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|
| Easy-On Back Flip FPC Connector with Lock Terminal, 0.30mm Pitch, LA75 Series, Right-Angle, Surface Mount, Dual Contact Style, 0.75mm Height, 61 Circuits | <u>5047546100</u> |

---

This document was generated on Jun 03, 2026