Product Line

- DeepTronica
- Single Pair Ethernet
- ZConnect
- Ceres
- X-Lok
- M Series
  - Accessory
  - M5
  - Guided M8
  - M8
  - M10.5
  - M12 (A)
  - M12 (B)
  - M12 (D)
  - M12 (I)
  - M12 (K)
  - M12 (L)
  - M12 (S)
  - M12 (T)
  - M12 (X)
  - M23
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
- RJ
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- RF
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub





M8S-04PFFT-EE0001

- Operating Temperature: -55°C ~ +125°C
- Transmission Speed: N/A
- Shielded: Plastic, Shielded
- Jacket Material: N/A
- Certificate: UL2238

You must login first for view the price


Quantity − 1 + Check Stock

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type Search



M Series, M8, A...	M Series, M8, A...	M Series, M8, A...	M Series, M8, A...	M Series, M8, A...	M Series, M8, A...
8P-04AMMM-... -20°C ~ +80°C	8P-04AMMM-... -20°C ~ +80°C	8P-04AMMM-... -20°C ~ +80°C	8P-04AMMM-... -20°C ~ +80°C	8P-04AMMM-... -20°C ~ +80°C	8P-04AMMM-... -20°C ~ +80°C
− 0 +	− 0 +	− 0 +	− 0 +	− 0 +	− 0 +

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current **3A**	Connector Type **SMT**
Shielded **Plastic, Shielded**	No. of Contacts **04**
Connector Gender **Female**	Backshell **N/A**
Mating Style **N/A**	IP Rating **Non-waterproof**
Assembly Style **SMT 180°**	

More Options

People Also Bought



M8S-04PFFT-EE0001	1CD-09AMFM-SL7A10	DC-05AFFM-QL8E14	M12A-05PMMC-...	CD-02AFFM-RL7A02

Downloaded from Arrow.com.