

SEARCH



[Labels](#) / [Circuit Board Labels](#) / [Not for Wash Polyester Labels](#) /

3" Core Series WorkHorse Glossy Polyester Labels



3" Core Series WorkHorse Glossy Polyester Labels

Part Number:

THT-38-423-10

Label/Tape Size:

0.375 in H x 0.375 in W

Material:

Polyester

For Use with Printer:

BBP®81 Label Printer, BRADY IP® Series
Label Printer, BradyPrinter i7100,
BRADYPRINTER PR Plus Series Label Printer

Material Number:

B-423

Color:

White

ADD TO CART

1

PEOPLE ALSO VIEWED

OVERVIEW

Permanent Polyester (B-423) is ideal for electronic PCB and component identification, bar code labels, rating plates and solar panel identification.

- Glossy white finish with permanent acrylic is thermal transfer printable
- RoHS compliant to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC; UL approved; CSA accepted
- Meets requirements of a halogen-free material per DIN VDE 0472 part 815
- Service temperature of -94 to 230° F (-70 to 110° C)

SPECIFICATIONS

Anti-Skid Surface?	N/A
Material Number	B-423
Dimensions	0.375 in H x 0.375 in W
UOM	Roll of 10000 Labels
Finish	Gloss
Indoor or Outdoor Use	Outdoor Use

Label/Tape Size	0.375 in H x 0.375 in W
Maximum Service Temperature °F	230 °F
Minimum Service Temperature °F	-94 °F
Printable Area Dimensions	0.375 in H x 0.375 in W
Printable Area Height	0.375 in
Printable Area Width	0.375 in
Product Number	30214
UPC	662820302148
Quantity per Roll	10000
Quantity per Row	7
Secondary Label Included	Secondary Label is Not Included
Tamper Indication Type	N/A
Thickness	0.003 in
Trade Name	WorkHorse® ToughBond®
Adhesive Type	Acrylic
Applications	Asset Tracking, Barcode Labeling, Circuit Board ID - Through Hole Top, Component & Equipment ID, General & Industrial ID, Rating Plates
Color	White
For Use with Printer	BBP®81 Label Printer, BRADY IP® Series Label Printer, BradyPrinter i7100, BRADYPRINTER PR Plus Series Label Printer
Label/Media Format	Roll
Material	Polyester
Material Properties	N/A
Print Technology	Thermal Transfer
Resistance Properties	Abrasion-Resistant, Chemical-Resistant, Corrosion-Resistant, Humidity-Resistant, UV-Resistant, Weather-Resistant
Shape	Square
Suggested Ribbon Series	R4900, R6000, R6200

Solutions

Floor Marking Guide
GHS Label Compliance

Services

Lockout Tagout Services
Arc Flash Services

Help

Contact Us
Knowledge Center

Resources

Find a Distributor
Printer Selection Tool

Lockout Tagout Compliance

Arc Flash Labeling Requirements

Cable and Wire Label Options

Product and Barcode Labeling

Brand Protection Solutions

Confined Space Services

Visual Workplace Services

Hazcom GHS Services

Software Programming & Integration

Label Template & File Conversion

Printer Use & Training

Printer Preventative Maintenance

Toll and Custom Coating

Authentication & Tracking Services

Printer Drivers & Firmware

Brady Software Updates

Safety Data Sheets

Technical Data Sheets

WEEE-RoHS Compliance


Product Certification

Printer Registration

Label Selection Tool

Digital Catalog

Request a Catalog




Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.

Contact
6555 W. Good Hope Rd. Milwaukee WI 53223
Phone: 888-250-3082
Hours: 7am-6pm CST
Monday - Thursday; Friday 7am-5pm CST

About
Corporation
Privacy Policy
Terms and Conditions
Terms of Use
ISO Certificates

Other
Brady Sites
Distributor Portal
International Sites
Safety Services & Software
Smart ID
Brand Protection



© 2018 Brady Worldwide, Inc.