**Part Number :** 765303040
**Product Description :** Impact 100 Ohm 5 Pair Mezzanine Receptacle, 40mm Stack Height, Left Guided, 10 Columns, 150 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free
**Series Number :** 76530
**Status :** Active
**Product Category :** Backplane Connectors



## Documents and Resources

### Drawings

765303040_sd.pdf

PK-70873-0040-001.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

SYM-76530-3040-001.zip

EE-76530-0040-001.pdf

SP-76530-0028-002.zip

SP-76530-0038-002.zip

SP-76530-0040-001.zip

### Specifications

AS-76060-990-001.pdf

AS-76060-9999-001.pdf

PS-45499-002-001.pdf

PS-76060-999-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |

Downloaded from Arrow.com.

| | |
|---|---|
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)6375-DC (05 Nov 2025) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Backplane Connectors |
| Series | 76530 |
| Description | Impact 100 Ohm 5 Pair Mezzanine Receptacle, 40mm Stack Height, Left Guided, 10 Columns, 150 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free |
| Application | Mezzanine |
| Component Type | PCB Receptacle |
| Product Name | Impact |
| UPC | 883906495800 |

### Agency

Downloaded from Arrow.com.

| | |
|---|---|
| CSA | LR19980 |
| UL | E29179 |

## Electrical

| | |
|---|---|
| Current - Maximum per Contact | 0.75A |
| Data Rate | 25.0 Gbps |
| Impedance | 100Ω |
| Shielded | No |
| Shield Type | N/A |
| Voltage - Maximum | 30V AC (RMS)/DC |

## Physical

| | |
|---|---|
| Circuits (Loaded) | 150 |
| Circuits (maximum) | 150 |
| Color - Resin | Black |
| Durability (mating cycles max) | 200 |
| First Mate / Last Break | No |
| Flammability | 94V-0 |
| Guide to Mating Part | Yes |
| Keying to Mating Part | No |
| Material - Metal | High Performance Alloy (HPA) |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Material - Resin | High Temperature Thermoplastic |
| Net Weight | 26.923/g |
| Number of Columns | 10 |
| Number of Pairs | 5 |
| Number of Rows | 15 |
| Orientation | Vertical |
| Packaging Type | Tray |
| PCB Locator | No |
| PCB Retention | Yes |
| PCB Thickness - Recommended | 1.60mm |
| PC Tail Length | 1.20mm |
| Pitch - Mating Interface | 1.90mm |

Downloaded from Arrow.com.

| | |
|---|---|
| Pitch - Termination Interface | 1.90mm |
| Plating min - Mating | 0.762µm |
| Polarized to PCB | Yes |
| Stackable | Yes |
| Temperature Range - Operating | -55° to +85°C |
| Termination Interface Style | Through Hole - Compliant Pin |

### Solder Process Data

| | |
|---|---|
| Lead-Free Process Capability | N/A |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| Impact 100 Ohm 5 Pair Vertical Backplane Headers | 76055 |

## Application Tooling



Downloaded from Arrow.com.