Part Number : 2008750002
Product Description : Micro-Fit TPA Free-Hanging Plug Housing, Single Row, 2 Circuits, UL 94V-0, Low-Halogen, Black
Series Number : 200875
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

2008750002_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

430450001-AS-000.pdf

2008750000-PK-000.pdf

430450001-PS-KO-000.pdf

430450001-PS-SP-000.pdf

PS-43045-001.pdf

436500001-PS-JA-000.pdf

436500001-PS-KO-000.pdf

436500001-PS-SP-000.pdf

PS-43650-001.pdf

2008750000-TS-000.pdf

430450007-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant

Downloaded from Arrow.com.

REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	200875
Description	Micro-Fit TPA Free-Hanging Plug Housing, Single Row, 2 Circuits, UL 94V-0, Low-Halogen, Black
Application	Wire-to-Wire
Component Type	Plug
Product Name	Micro-Fit TPA
UPC	191128228824

Agency

CSA	LR19980
UL	E29179

Physical

Downloaded from Arrow.com.

Circuits (maximum)	2
Color - Resin	Black
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.349/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-Fit TPA Single Row Receptacle Housings	171850
Micro-Fit 3.0 Single Row Receptacle Housings	43645
Micro-Fit TPA-to-Micro-Fit TPA Off-the-Shelf (OTS) Cable Assemblies	145132
Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female Off-the-Shelf (OTS) Cable Assemblies	214750
Micro-Fit 3.0 Female-to-Pigtail Off-the-Shelf (OTS) Cable Assemblies	214751

Use with Part(s)

Description	Part Number

Downloaded from Arrow.com.

Micro-Fit Male Crimp Terminals	43031
Use With	Micro-Fit 3.0 Male TPA Crimp Terminal 43031 (extension -5xxx only)

Downloaded from Arrow.com.