| ITEM NO. | PART NUMBER | DESCRIPTION | QTY. | COMPONENT NOTES |
|---|---|---|---|---|
| 1 | 50-00983 | Connector, 8 pin M12 A-code socket, 12xL22mm, gold plated, molding style, solder cup, IP67, shielded | 1 | |
| 2 | 50-00990 | Connector, 8 pin M12 A-code plug, 12xL22mm, gold plated, molding style, solder cup, IP67, shielded | 1 | |
| 3 | 30-01611 | Wire, 8C TS, 24 AWG, UL20387, 300V, 105C, 60C oil, UV, 6.8 mm, shielded, VW-1, PVC, 80A, black | 1 | |
| 4 | 24-00361 | Overmold, M12 plug and jack, 90° | 2 | PVC, black |




**Notes:**
Cable rated for 30 V, 2 A
Temperature: -40 ~ 105 °C
Oil resistant up to 60 °C
Water resistant up to 75 °C
UV resistant

IP67 waterproof rating when mated with corresponding (IP67) connector

Functionally equivalent components may be substituted

| Wiring Diagram | | |
|---|---|---|
| 50-00983 | wire color | 50-00990 |
| 1 | red | 1 |
| 2 | yellow | 2 |
| 3 | black | 3 |
| 4 | white | 4 |
| 5 | orange | 5 |
| 6 | blue | 6 |
| 7 | green | 7 |
| 8 | purple | 8 |
| Shell | shield/drain | Shell |

| Revision: | Date: | Description: |
|---|---|---|
| A | 12/30/2021 | Initial release |
| | | |
| | | |
| | | |
| | | |

Prepared: PB Digitally signed by PB Date: 2022.01.21 16:14:58 -08'00'

Verified: MP Digitally signed by MP Date: 2022.01.24 13:43:52 -08'00'

Dimensions are in millimeters.
Tolerances:
X: ± 0.5 mm
X.X: ± 0.3 mm
X.XX: ± 0.05 mm

Notes:

RoHS compliant

Function test: no open, no short circuit, no intermittent

Description:

Cable, 5000 mm, 0.8 mm 8C 90° 50-00983 M12 socket to 0.8 mm 90° 50-00990 M12 plug, 24 AWG, 30-01611 wire


TENSILITY
tel 1.541.323.3228 800 877.670.7118
fax 1.541.323.4202 web tensility.com


Size: A

Part number: 10-04998

Scale: 1:1

Sheet 1 of 1

5 4 3 2 1


To see a custom version of this cable assembly, call Tensility at 541-323-3228 or email engineering@tensility.com

Downloaded from Arrow.com.