Part Number : 897616791
Product Description : MMCX Right-Angle Plug to MMCX Right-Angle Plug on RG-316 Cable, 304.80mm Length, 50 Ohms
Series Number : 89761
Status : Active
Product Category : RF Cable Assemblies



Documents and Resources

Drawings

897616791_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; 1,1'-(ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF Cable Assemblies
Series	89761
Description	MMCX Right-Angle Plug to MMCX Right-Angle Plug on RG-316 Cable, 304.80mm Length, 50 Ohms
Application	RF
Assembly Configuration	Dual Ended Connectors
Connector to Connector	MMCX-to-MMCX
Product Name	MMCX
Type	RF Cable Assembly
UPC	883906707606

Electrical

Frequency	6 GHz
Impedance	50Ω

Physical

Cable Length	304.80mm
Gender	Plug/Plug
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Resin	PTFE
Net Weight	6.855/g
Packaging Type	Bag
Single Ended	No
Wire/Cable Type	RG-316

Downloaded from Arrow.com.

Mates With / Use With

Mates with Part(s)

Description	Part Number
MMCX Plugs and Jacks	73414

This document was generated on Jun 14, 2026

Downloaded from Arrow.com.