Honeywell

→ Honeywell.com → Automation & Control Solutions

Honeywell Sensing and Control

Search

narrow your search

Products
- Controls Monitoring and Lighting (354)
- Machine Safety (1726)
- Sensors (7074)
- Switches (9814)

Technology
- Control and Instrumentation (1063)
- Electromechanical (9357)
- Microstructure (2328)
- Optical/Infrared (1077)
- Thick Film (1764)
- More...

Need Help?
Click here to contact us

363P20K Trimmers

(Home : Products)



Actual product appearance may vary.

363 Series Trimmer, 20 kOhm, 0.5 W, 1 Turns, Square Body, Vertical Shaft

Sales & Service | Distributor Inventory

Overview | **Specs** | Documentation | Application Notes

Product Specifications

Product Type	Trimmer
Watts	0.5 W
Turns	1
Element Type	Cermet
Resistance Value	20 kOhm
Resistance Tolerance	± 10 %
Temperature Coefficient	± 100 ppm/ °C
Body	9,53 mm [0.375 in] square
Shaft Location	Vertical
Rotational Life	200 cycles
Series Name	363
Availability	Global
UNSPSC Code	4111363300
UNSPSC Commodity	4111363300 Potentiometers

Terms & Conditions | Privacy Statement | Site Map

Downloaded from Arrow.com.