

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0010311068**
Status: **Contact Molex**
Description: 5.00/7.50mm (.197/.295") Pitch SPOX™ Header, Vertical, with Friction Lock, 6 Circuits

Documents:

3D Model	Product Specification PS-5289-001 (PDF)
Drawing (PDF)	Packaging Specification SPK-5289-001 (PDF)
Product Specification PS-5199-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-5199-002 (PDF)	

Agency Certification

CSA	LR19980
TUV	R72090224
UL	E29179

General


Product Family	PCB Headers
Series	5289
Application	Power, Wire-to-Board
Product Name	SPOX™

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-2
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.60mm (.142")
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Bag
Pitch - Mating Interface	5.00mm (.197")
Plating min - Mating	5.080µm (200µ")
Plating min - Termination	5.080µm (200µ")
Polarized to PCB	Yes
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	7A
-------------------------------	----



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[5289Series](#)

Mates With

[5199 SPOX™ Crimp Terminal Housing](#)

Voltage - Maximum

250V

Material Info

Old Part Number

5289-6A

Reference - Drawing Numbers

Packaging Specification

SPK-5289-001

Product Specification

PS-5199-001, PS-5199-002, PS-5289-001,

RPS-5199-001

Sales Drawing

SD-5289-004

This document was generated on 05/16/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION