





Pin plugs SLZF 5.08/270

new





Pin plugs SLZF 5.08/270B

new



Coupler headers SL 5.08 KU



Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	12	10	15
Wire size (mm ² /AWG)	2.5	26...12	26...14

*Pollution severity 3 / Overvoltage category III

Additional technical data see page 224

Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	12	10	15
Wire size (mm ² /AWG)	2.5	26...12	26...14

*Pollution severity 3 / Overvoltage category III

Additional technical data see page 224

Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	12	15	10

*Pollution severity 3 / Overvoltage category III

Color

Poles	Type	Part No.	Part No.	Qty.
2	SLZF 5.08/2/270	1688430000	1688660000	100
3	SLZF 5.08/3/270	1688440000	1688670000	100
4	SLZF 5.08/4/270	1688450000	1688680000	100
5	SLZF 5.08/5/270	1688460000	1688690000	50
6	SLZF 5.08/6/270	1688470000	1688700000	50
7	SLZF 5.08/7/270	1688480000	1688710000	50
8	SLZF 5.08/8/270	1688490000	1688720000	50
9	SLZF 5.08/9/270	1688500000	1688730000	50
10	SLZF 5.08/10/270	1688510000	1688740000	50
11	SLZF 5.08/11/270	1688520000	1688750000	50
12	SLZF 5.08/12/270	1688530000	1688760000	50
13	SLZF 5.08/13/270	1688540000	1688770000	50
14	SLZF 5.08/14/270	1688550000	1688780000	50
15	SLZF 5.08/15/270	1688560000	1688790000	50
16	SLZF 5.08/16/270	1688570000	1688800000	50
17	SLZF 5.08/17/270	1688580000	1688810000	20
18	SLZF 5.08/18/270	1688590000	1688820000	20
19	SLZF 5.08/19/270	1688600000	1688830000	20
20	SLZF 5.08/20/270	1688610000	1688840000	20
21	SLZF 5.08/21/270	1688620000	1688850000	20
22	SLZF 5.08/22/270	1688630000	1688860000	20
23	SLZF 5.08/23/270	1688640000	1688870000	20
24	SLZF 5.08/24/270	1688650000	1688880000	20

Accessories	Page
Mounting	-
Marking	190
Coding	192, 193
Miscellaneous	201, 202

Color

Poles	Type	Part No.	Part No.	Qty.
2	SLZF 5.08/2/270B	1706140000	1706370000	100
3	SLZF 5.08/3/270B	1706150000	1706380000	100
4	SLZF 5.08/4/270B	1706160000	1706390000	100
5	SLZF 5.08/5/270B	1706170000	1706400000	50
6	SLZF 5.08/6/270B	1706180000	1706410000	50
7	SLZF 5.08/7/270B	1706190000	1706420000	50
8	SLZF 5.08/8/270B	1706200000	1706430000	50
9	SLZF 5.08/9/270B	1706210000	1706440000	50
10	SLZF 5.08/10/270B	1706220000	1706450000	50
11	SLZF 5.08/11/270B	1706230000	1706460000	50
12	SLZF 5.08/12/270B	1706240000	1706470000	50
13	SLZF 5.08/13/270B	1706250000	1706480000	50
14	SLZF 5.08/14/270B	1706260000	1706490000	50
15	SLZF 5.08/15/270B	1706270000	1706500000	50
16	SLZF 5.08/16/270B	1706280000	1706510000	50
17	SLZF 5.08/17/270B	1706290000	1706520000	20
18	SLZF 5.08/18/270B	1706300000	1706530000	20
19	SLZF 5.08/19/270B	1706310000	1706540000	20
20	SLZF 5.08/20/270B	1706320000	1706550000	20
21	SLZF 5.08/21/270B	1706330000	1706560000	20
22	SLZF 5.08/22/270B	1706340000	1706570000	20
23	SLZF 5.08/23/270B	1706350000	1706580000	20
24	SLZF 5.08/24/270B	1706360000	1706590000	20

Accessories	Page
Mounting	187
Marking	190
Coding	192, 193
Miscellaneous	201, 202

Color

Poles	Type	Part No.	Qty.
2	SL 5.08/2KU	1597760000	100
3	SL 5.08/3KU	1597770000	100
4	SL 5.08/4KU	1597780000	50
5	SL 5.08/5KU	1597790000	50
6	SL 5.08/6KU	1597800000	50
7	SL 5.08/7KU	1597810000	50
8	SL 5.08/8KU	1597820000	50
9	SL 5.08/9KU	1597830000	50
10	SL 5.08/10KU	1597840000	50
11	SL 5.08/11KU	1597850000	50
12	SL 5.08/12KU	1597860000	50
13	SL 5.08/13KU	1597870000	50
14	SL 5.08/14KU	1597880000	50
15	SL 5.08/15KU	1597890000	50
16	SL 5.08/16KU	1597900000	50
17	SL 5.08/17KU	1597910000	20
18	SL 5.08/18KU	1597920000	20
19	SL 5.08/19KU	1597930000	20
20	SL 5.08/20KU	1597940000	20
21	SL 5.08/21KU	1597950000	20
22	SL 5.08/22KU	1597960000	20
23	SL 5.08/23KU	1597970000	20
24	SL 5.08/24KU	1597980000	20

Accessories	Page
Mounting	-
Marking	-
Coding	-
Miscellaneous	-