© 2018 TE Connectivity Ltd. family of companies. All Rights Reserved



Feedback

ACTIVE

03 MODII HDR SRST B/A .100CL

AMPMODU | AMPMODU Headers

TE Part # **102976-3**
TE Internal #: **102976-3**

Connector Assembly Type : **PCB Mount Header**
PCB Mount Orientation : **Vertical**

+ More

Add to List | Similar Products

ORDER SAMPLES

Compatible Parts & Tooling

Please give us feedback:
Did you find what you need on this page?

YES NO

Downloaded from Arrow.com.

DOCUMENTS

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Assembly Type : **PCB Mount Header**
Connector & Contact Terminates To : **Printed Circuit Board**
Header Type : **Breakaway**
Row-to-Row Spacing : **2.54 mm [.1 in]**
Gasket : **Without**
Product Type : **Connector**
Stabilizers : **Without**
Connector Type : **Connector Assembly**
Board Standoff : **Without**
Strain Relief : **Without**

Feedback

Configuration Features

Selectively Loaded : **No**
PCB Mount Orientation : **Vertical**
Number of Positions : **3**
Number of Rows : **1**
Keyed : **No**

Electrical Characteristics

Dielectric Withstanding Voltage : **750 V**

Body Features

Post Size : **.64 mm [.025 in]**

Downloaded from Arrow.com.

Contact Features

Contact Base Material : **Phosphor Bronze**
PCB Contact Termination Area Plating Material : **Tin-Lead**
Contact Underplating Material : **Nickel**
Contact Protection : **Without**
Contact Shape : **Square**
Contact Type : **Pin**
Contact Current Rating (Max) (A): **3**
Contact Mating Area Plating Thickness (µin): **30**
Contact Mating Area Plating Material : **Gold**

Feedback

Termination Features

Termination Method to PC Board : **Through Hole**
Termination Post Length : **3.18 mm [.125 in]**
Termination End Plating Thickness (µin): **100 – 200**
Termination End Plating Material : **Tin-Lead over Nickel**

Mechanical Attachment

PCB Mount Retention : **Without**
Panel Mount Feature : **Without**
Mating Connector Lock : **Without**
PCB Mounting Style : **Through Hole**

Housing Features

Centerline (Pitch) : **2.54 mm [.1 in]**
Housing Material : **Thermoplastic**
Housing Color : **Black**

Dimensions

Mating Post Length : **8.08 mm [.318 in]**

Downloaded from Arrow.com.

Usage Conditions

Operating Temperature Range (°C): **-65 – 105**

High Temperature Housing : **No**

Operation/Application

High Speed Serial Data Connector : **No**

Industry Standards

Approved Standards : **CSA LR7189, UL E28476**

UL Flammability Rating : **UL 94V-0**

Feedback

Packaging Features

Packaging Quantity : **540**

Packaging Method : **Carton**

Other

Comment : **Headers may be broken to desired number of positions using Hand Tool No. 91406-1, or Tool Kit No. 314818-1. Other tail lengths are available, consult TE Connectivity.**

PRODUCT COMPLIANCE +

Compatible Parts

Downloaded from Arrow.com.



TE Part # 487378-2

003 HOUSING FFC RCPT 100CL SR

View Product

Feedback

Also in the Series | AMPMODU Headers



Automotive, Truck, Bus, & Off-Road Headers (1)



Board-to-Board Headers & Receptacles (2299)



Multiple Configuration PCB Connector Contacts (84)

Customers Also Bought

Downloaded from Arrow.com.



TE Part # 102977-6

12 MODII HDR DRST B/A .100CL



TE Part # 5-146253-4

08 MODII HDR DRST B/A .100CL LF



TE Part # 5406721-1

MJ, RJ45, SMT, GRAY, 22"REEL

Feedback

Downloaded from Arrow.com.