

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0150180061

Status:

Active

Overview:

FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers

Description:

0.50mm Pitch Premo-Flex FFC Jumper with Ears, Same Side Contacts (Type A), 152.00mm Cable Length, Gold (Au) Plating, 6 Circuits

Documents:


Drawing (PDF)

Product Specification 150180001-000 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

|                               |                                                           |
|-------------------------------|-----------------------------------------------------------|
| General                       |                                                           |
| Product Family                | Cable                                                     |
| Series                        | 15018                                                     |
| Comments                      | Contacts on the same side, Type A                         |
| Crimp Quality Equipment       | Yes                                                       |
| Overview                      | FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers |
| Product Name                  | Premo-Flex FFC Jumper                                     |
| Taxonomy                      | Flexible Printed Circuit (FPC)                            |
| UPC                           | 193264329113                                              |
| Physical                      |                                                           |
| Cable Length                  | 152.00mm                                                  |
| Circuits (Loaded)             | 6                                                         |
| Contact Layout Type           | A (same side)                                             |
| Material - Plating Mating     | Gold                                                      |
| Packaging Type                | Bag                                                       |
| Pitch - Mating Interface      | 0.50mm                                                    |
| Temperature Range - Operating | -40° to +105°C                                            |
| Wire Size AWG                 | N/A                                                       |
| Wire/Cable Type               | Flat Flex Cable                                           |
| Electrical                    |                                                           |
| Current - Maximum per Contact | 0.5A                                                      |
| Voltage - Maximum             | 60V AC                                                    |
| Material Info                 |                                                           |
| Reference - Drawing Numbers   |                                                           |
| Product Specification         | 150180001-000                                             |
| Sales Drawing                 | SD-15018-001-001                                          |



Series image - Reference only

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained per - D(2022)9120-DC (17 Jan 2023)              |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Low-Halogen                                               |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

15018 Series

Mates With

Easy-On FFC/FPC Connector [5051100692](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION