

Cable sleeve - CES-LRG-BK-15



0801619

<https://www.phoenixcontact.com/us/products/0801619>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Large, slotted cable sleeves suitable for cables with a diameter of 14 ... 15 mm, material: NBR



Product Description

Slotted sleeves for accommodating pre-assembled cables and lines with a diameter of 4 mm ... 5 mm, can be used in CES sealing frames.

Cable sleeve - CES-LRG-BK-15



0801619

<https://www.phoenixcontact.com/us/products/0801619>

Commercial Data

Item number	0801619
Packing unit	1 pc
Minimum order quantity	10 pc
Sales Key	B10
Product Key	BF7CCX
Catalog Page	Page 678 (C-2-2019)
GTIN	4046356674256
Weight per Piece (including packing)	34.59 g
Weight per Piece (excluding packing)	31.65 g
Customs tariff number	40169997
Country of origin	TW

Cable sleeve - CES-LRG-BK-15

0801619

<https://www.phoenixcontact.com/us/products/0801619>




Technical Data

Product properties

Product type	Cable sleeve
No. of conductors	1

Dimensions

Dimensional drawing	
Width	39 mm
Height	17 mm
Length	53 mm

Material specifications

Color	black
Material	NBR
Material	NBR

Connector

Seal size	large
-----------	-------

Cable / line

Cable structure	
External cable diameter	1x 14 mm ... 15 mm

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP54
Ambient temperature (operation)	-40 °C ... 125 °C (static)


Cable sleeve - CES-LRG-BK-15

0801619

<https://www.phoenixcontact.com/us/products/0801619>



Drawings



Dimensional drawing

Cable sleeve - CES-LRG-BK-15

0801619

<https://www.phoenixcontact.com/us/products/0801619>



Approvals

DNV

Approval ID: TAE00003VJ

Cable sleeve - CES-LRG-BK-15



0801619

<https://www.phoenixcontact.com/us/products/0801619>

Classifications

ECLASS

ECLASS-9.0	27144425
ECLASS-10.0.1	27144425
ECLASS-11.0	27144425

ETIM

ETIM 8.0	EC000451
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Cable sleeve - CES-LRG-BK-15



0801619

<https://www.phoenixcontact.com/us/products/0801619>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Cable sleeve - CES-LRG-BK-15

0801619

<https://www.phoenixcontact.com/us/products/0801619>



Accessories

Filler plugs

Filler plugs - KDT-ST 15 - 3062045

<https://www.phoenixcontact.com/us/products/3062045>

Filler plugs, length: 20 mm, diameter: 15 mm



Phoenix Contact 2022 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com