

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

4

3

2



1

# LENGTH

| REV. | DESCRIPTION        | REVISIONS | DATE     | APPROVED |
|------|--------------------|-----------|----------|----------|
| A    | NEW RELEASE        |           | 31/07/06 |          |
| A1   | Change Part Number |           | 17/11/06 |          |



4-40thread(UNC)

4X THUMBSCREW



Amphenol Cables on Demand

A






D-SUB

26PIN Male

0.315± 0.008

D-SUB  
26PIN Female



SEC A-A

PIN OUT: 1 TO 1

| Male  | Female | Male   | Female |
|-------|--------|--------|--------|
| PIN1  | PIN1   | PIN16  | PIN16  |
| PIN2  | PIN2   | PIN17  | PIN17  |
| PIN3  | PIN3   | PIN18  | PIN18  |
| PIN4  | PIN4   | PIN19  | PIN19  |
| PIN5  | PIN5   | PIN20  | PIN20  |
| PIN6  | PIN6   | PIN21  | PIN21  |
| PIN7  | PIN7   | PIN22  | PIN22  |
| PIN8  | PIN8   | PIN23  | PIN23  |
| PIN9  | PIN9   | PIN24  | PIN24  |
| PIN10 | PIN10  | PIN25  | PIN25  |
| PIN11 | PIN11  | PIN26  | PIN26  |
| PIN12 | PIN12  | SHIELD | SHIELD |
| PIN13 | PIN13  |        |        |
| PIN14 | PIN14  |        |        |
| PIN15 | PIN15  |        |        |

## LENGTH & P/N Table

| LENGTH         | P/N                  | Cable Color |
|----------------|----------------------|-------------|
| 2.5FT ± 1 inch | CS-DSDHDD26MF0-002.5 | GREY        |
| 5FT ± 2 inch   | CS-DSDHDD26MF0-005   | GREY        |
| 10FT ± 3 inch  | CS-DSDHDD26MF0-010   | GREY        |
| 15FT ± 3 inch  | CS-DSDHDD26MF0-015   | GREY        |
| 25FT ± 4 inch  | CS-DSDHDD26MF0-025   | GREY        |
| 50FT ± 8 inch  | CS-DSDHDD26MF0-050   | GREY        |

UNLESS OTHERWISE SPECIFIED  
DIMENSIONS ARE IN INCHES  
TOLERANCES ARE:

| DESCRIPT | ANGLES |
|----------|--------|
| .X       | ±X°    |
| .XX      | ±XX°   |
| .XXX     | ±XXX°  |

THIRD ANGLE PROJECTION



Amphenol Cables on Demand

20 VALLEY ST. ENDCOTT, NY 13760

ASM CBL Deluxe High Density  
26PIN D-Sub MF

| SIZE | DWG. NO.           | REV. |
|------|--------------------|------|
| A    | CS-DSDHDD26MF0-XXX | A1   |

CAD FILE

WFG ENG

SCALE

SHEET

OF

