


[Connectors](#) > [Automotive Connectors: Car, Truck, Bus, & Off-Road](#) > [Data Connectivity Systems](#) > [Data Connectivity Housings](#)

JACK HOUSING, 2 POSN, FAKRA, Key D,CpSlT



✓ ACTIVE

FAKRA RF Connector System

TE Part # **5-1924855-4**

TE Internal #: **5-1924855-4**

Connector Style : **Housing for Male Terminals**

Keying : **D**

Connector System : **Wire-to-Wire**

Number of Positions : **2**

Sealable : **No**

Add to List ▾

[Similar Products](#)



ORDER SAMPLES

Compatible Parts & Tooling

SHOP OUR DISTRIBUTORS

North America ▾

Request pricing, availability and customization options

CONTACT US



We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

DOCUMENTS

FEATURES

PRODUCT COMPLIANCE

Product Drawings

JACK HOUSING, 2 POSN, FAKRA, Key D,CpSlT

[JACK HOUSING, 2 POSN, FAKRA, Key D,CpSlT](#)
English

CAD Files

3D PDF

[3D_CVM_CVM_5-1924855-4_H.pdf](#) 3D

Customer View Model

[ENG_CVM_CVM_5-1924855-4_H.2d_dxf.zip](#)
English

[ENG_CVM_CVM_5-1924855-4_H.3d_igs.zip](#)
English

[ENG_CVM_CVM_5-1924855-4_H.3d_stp.zip](#)
English

Product Specifications

Application Specification

[ENG_SS_114-13157_V.pdf](#) English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type
Features

Hybrid Connector : **No**

Connector Style : **Housing for Male Terminals**

Connector System : **Wire-to-Wire**

Sealable : **No**

Connector & Contact Terminates To :
Wire & Cable

Board Standoff : **Without**

Configuration
Features

Keying : **D**

Number of Positions : **2**

Fiber Optic Transceiver : **Without**

Snap-Lock : **Without**

Body Features

Body Material : **PBT GF**

Cable Exit Type : **Fixed**

Ferrule : **Without**

Environmental Protection : **Other**

Cable Exit Angle : **180° (Inline)**

Contact Features

Center Contact Plating Material :
None

Contact Mating Area Plating Material :
None

Center Contact : **Without**

Housing Features

Housing Color : **Violet**

Dimensions

Width : **16.9 mm [.665 in]**

Length : **21.5 mm [.846 in]**

Height : **16.85 mm [.66 in]**

Usage Conditions

Operating Temperature (Max) (°C):
65, 70, 75, 80, 85

Operating Temperature (Max) (°F):
149, 158, 167, 176, 185

Cable Type : **Coax**

Operating Temperature Range :
-40 – 85 °C [-40 – 185 °F]

Operation/Application Circuit Application : **Signal**






Industry Standards	Agency/Standard : USCAR
Packaging Features	Packaging Quantity : 3500
Other	Dielectric Material : None
Statement of Compliance	Statement of Compliance pdf

Compatible Parts

 <p>TE Part # 1274233-1 SPACER, RG62U, MODIFIED</p> <p>View Product</p>	 <p>TE Part # 1274233-3 SPACER, RG71/U M</p> <p>View Product</p>	 <p>TE Part # 1-413889-3 FERRULE, NI PLTD</p> <p>View Product</p>	 <p>TE Part # 1274233-2 SPACER, RG62U</p> <p>View Product</p>
---	--	---	---

Also in the Series | FAKRA RF Connector System

 <p>Automotive Connector Caps & Covers (1)</p>	 <p>Automotive Connector EMC Shielding (3)</p>	 <p>Automotive Connector Locks & Position Assurance (2)</p>	 <p>Data Connectivity Headers (496)</p>
--	--	--	---

Customers Also Bought





TE Part # 5-776681-2
Jack Kit, 1 Pos, RG-59, Fakra, Unassembl



TE Part # 776681-2
Jack Kit, 1 Pos, RG-59, Fakra, Unassembl



TE Part # 1274233-3
SPACER, RG71/U M



TE Part # 2141494-5
1POS, CONTACT KIT, REC HSG, ASSY, CODE

About TE Connectivity

For Partners

Customer Support

CALL US

LIVE CHAT

United States

Our Company

Events

TE News Center

Careers


Investors

Corporate Responsibility

Terms and Conditions of Sale

Distributors

Suppliers

 Email or Call Us

 Find Authorized Distributors

 What's New on TE.com

 Product FAQs

Select Country & Language

United States (EN)


Germany (DE)

China (中文)

Japan (日本語)

Find Your Country/Region ▼

[Terms of Use](#) | [Privacy](#) | [Cookie Policy](#) | [Accessibility](#) | [Site Map](#)



© 2018 TE Connectivity. All Rights Reserved.