

## Crimping pliers - CRIMPFOX 6T - 1212037

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.25 mm² ... 6 mm², lateral entry, trapezoidal crimp

### Your advantages

- ✓ Comprehensive range of crimping pliers
- ✓ All ferrules can be optimally crimped with a minimum amount of effort even in the case of large conductor cross sections
- ✓ Marked die stations for precise processing of corresponding cross sections
- ✓ Consistently high crimping quality
- ✓ Unlockable pressure lock



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 454049
GTIN	4046356454049
Weight per Piece (excluding packing)	520.000 g
Custom tariff number	82032000
Country of origin	Sweden

### Technical data

#### Dimensions

Length (b)	220 mm
Width (a)	22.5 mm
Height (c)	72 mm

#### General

# Crimping pliers - CRIMPFOX 6T - 1212037

## Technical data

### General


Color	black
Compression	Trapezoidal crimp
Type of contact	Insulated and uninsulated ferrules
Min. cross section	0.25 mm <sup>2</sup>
Max. cross section	6 mm <sup>2</sup>
AWG min	24
AWG max	10
Weight	555 g

### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

## Drawings

Product drawing



## Classifications

### eCl@ss

eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

### ETIM

ETIM 2.0	EC001186
----------	----------

## Crimping pliers - CRIMPFOX 6T - 1212037

### Classifications

#### ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

#### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

### Approvals

#### Approvals

Approvals

EAC

Ex Approvals

#### Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

### Accessories

Accessories

Mounting material

## Crimping pliers - CRIMPFOX 6T - 1212037

### Accessories

Replacement spring - CRIMPFOX/ SPR-1 - 1212069



Spare recuperating spring

---

Phoenix Contact 2021 © - all rights reserved  
<http://www.phoenixcontact.com>