

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Jumper Bars

General Information

Extended Product Type:	BJMI5-3
Product ID:	1SNA176279R1700
EAN:	3472591762792
Catalog Description:	BJMI5-3 POLES Jumper Bars
Long Description:	- IP20 assembled screw jumper bars, - Fractionnable model with captive screws and spacers, - Allows connection between consecutive blocks only.

Ordering

Color:	Grey
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160001C0207-CH-J Accessories
Instructions and Manuals:	1SNC160001C0207-CH-J Accessories

Dimensions

Product Net Width:	5 mm
Product Net Height:	20.6 mm
Product Net Depth / Length:	5 mm
Product Net Weight:	5 g

Technical

Spacing:	5 mm
Function:	Jumper Bars
Rated Current (I_n):	Main Circuit 24 A
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Suitable For:	D1.5/5.ADO.NF D1/5.ADO D1/5.D2.ADO D2.5/5.ADO D2.5/5.D2.ADO MA2.5/5 MA2.5/5-2CPE MA2.5/5-CPE MA2.5/5D-2CPE
----------------------	--

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C
---------------------------------	---------------------------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225001C1009
--	-----------------

Instructions and Manuals:	1SNC160001C0207-CH-J Accessories
----------------------------------	----------------------------------

RoHS Information:	1SND230492F0201
--------------------------	-----------------

Classifications

Object Classification Code:	X
------------------------------------	---

ETIM 4:	EC000489 - Cross-connector for terminal block
----------------	---

ETIM 5:	EC000489 - Cross-connector for terminal block
----------------	---

ETIM 6:	EC000489 - Cross-connector for terminal block
----------------	---

Container Information

Package Level 1 Units:	10 piece
-------------------------------	----------

Package Level 1 Width:	155 mm
-------------------------------	--------

Package Level 1 Depth / Length:	200 mm
--	--------

Package Level 1 Height:	5 mm
--------------------------------	------

Package Level 1 Gross Weight:	0.05 kg
--------------------------------------	---------

Package Level 1 EAN:	3472591762792
-----------------------------	---------------

Package Level 2 Units:	500 piece
-------------------------------	-----------

Package Level 3 Units:	90000 piece
-------------------------------	-------------

Product Packing Type:	Bag
------------------------------	-----

