MICRO SWITCH
A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREEPORT, ILLINOIS
FED. MFR. CODE 91929

ASSEMBLY– TOGGLE SWITCH

CATALOG LISTING
6AT102



NOTE-
1-UNIT INCLUDES (1) CAT. LIST. 11SM106 BASIC SWITCH. (A)
2-TERMINALS ARE PLATED FOR SOLDERING.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

ELECTRICAL DATA

CONTACT ARRANGEMENT	BREAK DISTANCE
S. P. D. T.	.010 MIN.

250 VAC — 5 AMP
30 VOLTS DC RATING
INDUCTIVE — SEA LEVEL — 3 AMP
50,000 FT. — 2.5 AMP
RESISTIVE — SEA LEVEL — 5 AMP
50,000 FT. — 5 AMP
(B)
MAXIMUM INRUSH — 24 AMP

SCALE FULL
DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT .018 LB.

REVISIONS		
A	C.O. 11755	K.F.M. 26 JUNE 57
B	CO13507	M B F 2 APR 59
C	CO37377	K P K 30 JUL 76
D	CO 37753	GLH 3 NOV 76
E	CO-51446	KAG 12 MAY 82

6AT102	REPLACES		
M	RELEASE NO. SR 5681		
DRAWING NUMBER	9 OCT. '56		
X 6			
X X			
ISSUE	MJL	CHECK	
	9 OCT. '56		
	WRD	CHECK	
	15 OCT. '56		
	RLZ	CHECK	
	3 OCT. 56	DRAWN	R. E. R.

Downloaded from Arrow.com.