Welcome to TE.com, you are viewing information for visitors in United States CHOOSE ANOTHER SITE STAY ON THIS SITE

T4162113003-007

RPC-M12-3MS-10.0SH-M12-3FS-PVC





TE Internal #: **T4162113003-007**
TE Internal Description: **RPC-M12-3MS-10.0SH-M12-3FS-PVC**
All M12 A-CODE MS-FS DOUBLE ENDED CABLE (110)

Connector Type : **Plug/Receptacle**
Number of Positions : **3**
Keying : **A**
Housing Material : **GF Nylon**
Cable Assembly Type : **M12 to M12**

Compatible Parts & Tooling

We are here to help!
Get in touch with our product experts.

CHAT WITH US
EMAIL US
CALL US

Feedback

Documents | Features | Product Compliance

Product Description

M12 A-code Male Straight to Female Straight Assemblies are offered in 2 up to 5 positions PUR/PVC, Shielded & non-shielded, up to 10m length

View All M12 A-CODE MS-FS DOUBLE ENDED CABLE (110)

Product Drawings

RPC-M12-3MS-10.0SH-M12-3FS-PVC

RPC-M12-3MS-10.0SH-M12-3FS-PVC English

CAD Files

3D PDF

3D_CVM_CVM_T4162113003-007_A.pdf 3D

Customer View Model

ENG_CVM_CVM_T4162113003-007_A.2d_dxf.zip English

ENG_CVM_CVM_T4162113003-007_A.3d_igs.zip English

ENG_CVM_CVM_T4162113003-007_A.3d_stp.zip English

Datasheets & Catalog Pages

M8/M12 Sensor Actuator Cable Assemblies Datasheet

ENG_DS_1-1773966-2_0119.pdf English

Product Specification

Downloaded from Arrow.com.

Specifications	ENG_SS_108-106140_A3.pdf English ENG_SS_114-137144_A2.pdf English
Product Description	M12 A-code Male Straight to Female Straight Assemblies are offered in 2 up to 5 positions PUR/PVC, Shielded & non-shielded, up to 10m length View All M12 A-CODE MS-FS DOUBLE ENDED CABLE (110)

Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Assembly Type : **Pigtail** Connector Type : **Plug/Receptacle** Cable Assembly Type : **M12 to M12** Shielded : **Yes** Cable Type : **PVC** Product Type : **Cable Assembly** LED : **Without**
Configuration Features	Number of Positions : **3** Keying : **A** Configuration : **Double Ended**
Electrical Characteristics	Operating Voltage (VDC): **250** Operating Voltage (VAC): **250**
Body Features	Cable Jacket Color : **Black** Insulation Material : **PVC** Wire Color : **Brown, Blue, Black** Connector Color : **Blue** Conductor Material : **Copper Alloy** Environmental Protection : **With** Cable Exit Angle : **Straight**
Contact Features	Contact Current Rating (A): **4**
Mechanical Attachment	Screw & Hole Thread Size : **M12 x M12**
Housing Features	Housing Material : **GF Nylon**
Dimensions	Wire Size (mm^2): **.34** Wire Size (AWG): **22** Cable Assembly Length (mm): **10000**
Operation/Application	M8/M12 Application Type : **Sensor/Actuator**

Downloaded from Arrow.com.

Other	Field Serviceable : **Yes**

Detailed product compliance is not available. Please Contact Us

Statement of Compliance	Statement of Compliance pdf

Downloaded from Arrow.com.