

Part Number : 1060533500
Product Description : FC Connector, Multimode, 128µm Ferrule, .90mm Buffered Fiber, Metal Coupling Nut, Black Boot
Series Number : 86290
Status : Obsolete
Product Category : Fiber Optic Connectors
Engineering Part Number : 860533500

Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

Obsolete

Downloaded from Arrow.com.

General

Status	Obsolete
Category	Fiber Optic Connectors
Series	86290
Description	FC Connector, Multimode, 128µm Ferrule, .90mm Buffered Fiber, Metal Coupling Nut, Black Boot
Comments	Dust Cap Included But Not Shown
Mode	Multimode
Product Name	FC
UPC	822350267687

Physical

Angled Physical Contact (APC)	No
Boot Color	Black
Boot Type	Straight
Cable Size	900µm
Color - Resin	N/A
Ferrule Hole Size	128µm
Ferrule Material	Zirconia PC
Gender	Plug
Material - Housing	PBT
Mounting Style	Adhesive
Net Weight	6.750/g
Ports	1
Wire/Cable Type	Simplex

Solder Process Data

Lead-Free Process Capability	Product not active

Obsolete

Mates With / Use With

Mates with Part(s)

Description	Part Number
FC Adapters	106152

Downloaded from Arrow.com.

This document was generated on Sep 16, 2026

Obsolete

Downloaded from Arrow.com.