


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	RELEASED PER ECR-14-000965	22JAN2014	RG	MC
	B	REVISED PER ECO-16-017056	22NOV2016	RG	SH
	C	REVISED PER ECO-19-013178	27AUG219	TX	SH
	C1	REVISED AS PER ECR-25-243551	07MAY2025	AD	JM







1. MATERIAL: LCP, BLACK.
2. MATERIAL: PHOSPHOR BRONZE PER ASTM B 103.
3. FINISH: 0.76µm MIN GOLD PLATE PER ASTM B 488, APPLIES TO INTERFACE AREA AND 2.03µm MIN TIN PLATE SOLDER TAILS, ALL OVER 3.81µm MIN NICKEL PLATE PER QQ-N-290.
4. DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
5. FINISH: 0.38µm MIN GOLD PLATE PER ASTM B 488, APPLIES TO INTERFACE AREA AND 2.03µm MIN TIN PLATE SOLDER TAILS, ALL OVER 3.81µm MIN NICKEL PLATE PER QQ-N-290.
6. TAPE AND REEL PACKAGED.
7. MATERIAL: NICKEL SILVER ALLOY. C77000.
8. PACKAGE SPEC (TAPE&REEL): WIDTH 32mm X PITCH 16mm

FINISH	C	B	A	POSN	PART NUMBER
5	28.8	28.6	30.2	68	1-2007570-5
	16.8	16.6	18.1	38	1-2007570-4
	23.2	23	24.6	54	1-2007570-3
	21.6	21.4	23	50	1-2007570-2
	16	15.8	17.4	36	1-2007570-1
	12	11.8	13.4	26	1-2007570-0
3	28.8	28.6	30.2	68	2007570-6
	16.8	16.6	18.1	38	2007570-5
	23.2	23	24.6	54	2007570-4
	21.6	21.4	23	50	2007570-3
	16	15.8	17.4	36	2007570-2
	12	11.8	13.4	26	2007570-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.25
2 PLC ±0.13
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL: LCP 1, 2, 7
FINISH: 3, 5

DWN J. POLIGNONE 17JAN08
CHK E. BRIGHT 17JAN08
APVD E. BRIGHT 17JAN08
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME EVERCLEAR Mini-SAS, CONNECTOR ASSEMBLY, RECEPTACLE, RIGHT ANGLE, SURFACE MOUNT

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-2007570	

CUSTOMER DRAWING | SCALE 15:1 | SHEET 1 OF 3 | REV C1


4805 (3/13)

Downloaded from Arrow.com.


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



SCALE 15:1





UN-SPECIFIED DIMENSION ALL REFER TO SHEET 1

8	5	16.8	16.6	18.1	38	2-2007570-6
	5	16.8	16.6	18.1	38	1-2007570-6
	3	16.8	16.6	18.1	38	2007570-7
	FINISH	C	B	A	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.25
2 PLC ±0.13
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL TBD -

FINISH - -

DWN J. POLIGNONE 17JAN08
CHK E. BRIGHT 17JAN08
APVD E. BRIGHT 17JAN08

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

TE Connectivity

NAME EVERCLEAR Mini-SAS, CONNECTOR ASSEMBLY, RECEPTACLE, RIGHT ANGLE, SURFACE MOUNT

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-2007570	


CUSTOMER DRAWING | SCALE 15:1 | SHEET 2 OF 3 | REV C1

Downloaded from Arrow.com.

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



RECOMMEND PCB LAYOUT
SCALE 10:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.25
2 PLC ±0.13
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL TBD -

FINISH -

DWN	J. POLIGNONE	17JAN08
CHK	E. BRIGHT	17JAN08
APVD	E. BRIGHT	17JAN08
PRODUCT SPEC	-	
APPLICATION SPEC	-	
WEIGHT	-	

TE Connectivity

NAME: EVERCLEAR Mini-SAS, CONNECTOR ASSEMBLY, RECEPTACLE, RIGHT ANGLE, SURFACE MOUNT

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-2007570	

CUSTOMER DRAWING | SCALE 10:1 | SHEET 3 OF 3 | REV C1

4805 (3/13)

Downloaded from Arrow.com.