Part Number : 526102833
Product Description : Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 28 Circuits, Tin-Silver-Bismuth Plating
Series Number : 52610
Status : Obsolete
Product Category : FFC / FPC Connectors



Obsolete

Documents and Resources

Symbol and Footprint (Multi-Format)

Specifications

PS-52610-032-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	FFC / FPC Connectors
Series	Slider
Description	Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 28 Circuits, Tin-Silver-Bismuth Plating
Product Name	Easy-On
UPC	887191316284

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

Physical

Actuator Type	Slider
Circuits (Loaded)	28
Color - Resin	Natural
Contact Position	N/A
Durability (mating cycles max)	30
Flammability	94V-0
Mated Height	5.75mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin-Silver-Bismuth

Obsolete

Downloaded from Arrow.com.

Material - Plating Termination	Tin-Silver-Bismuth
Material - Resin	Nylon
Net Weight	1249.900/mg
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	No
PC Tail Length	2.00mm
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-40° to +85°C
Wire/Cable Type	FFC/FPC

Mates With / Use With

Mates with Part(s)

Description	Part Number
1.00mm Pitch Premo-Flex FFC Jumpers	15167
1.00mm Pitch Premo-Flex FFC Jumpers	15267
1.00mm Pitch Premo-Flex FFC Jumpers	98267

Obsolete

Downloaded from Arrow.com.