



Part Number : [5017848009](#)
Product Description : 0.50mm Pitch FFC-to-Board
Plug Jacket Cover, 80 Circuits
Series Number : 501784
Status : Active
Product Category : Connector Accessories



Documents and Resources

Drawings

[5017848009_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[5017848009.dxf](#)

Specifications

[5017832000-A00.pdf](#)

[SPK-501784-001-001.pdf](#)

[PS-501786-001-001.pdf](#)

[PS-501786-002-001.pdf](#)

[PS-501864-001-001.pdf](#)

[PS-501864-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	501784
Description	0.50mm Pitch FFC-to-Board Plug Jacket Cover, 80 Circuits
Comments	Requires a custom FFC with notches
Component Type	Jacket Cover
Product Name	Easy-On
UPC	822350232128

Agency

UL	E29179
----	--------

Physical

Circuits (Loaded)	80
Circuits (maximum)	80
Color - Resin	Black

Gender	Plug
Material - Resin	Polyester
Net Weight	232.463/mg
Packaging Type	Bag
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Use with Part(s)

Description	Part Number
0.50mm Pitch FFC-to-Board Connector Plug Jackets	<u>501783</u>
0.50mm Pitch Easy-On FFC/FPC-to-Board Vertical Receptacle Assemblies	<u>501786</u>
0.50mm Pitch Easy-On FFC/FPC-to-Board Right-Angle Receptacle Assemblies	<u>501864</u>

This document was generated on Apr 11, 2026