© 2016 TE Connectivity Ltd. family of companies. All Rights Reserved

CONNECTORS

CONNECTOR CONTACTS







✔ Active

TE CONNECTIVITY (TE)

5MM POWER KEY 3P PLUG HSG BLUE

Power Key | Power Key 5.0

2-2174299-3

TE Internal Number: 2-2174299-3

EU RoHS Compliant

EU ELV Compliant

Connector System Wire-to-Board

Contact Type Socket

Operating Voltage (VAC) 300

Contact Retention Without

Operating Temperature Range -30 – 105 °C [-22 – 221 °F]

PRODUCT DRAWING
Japanese

3D PDF

DOCUMENTATION

Product Drawings

5.0 POWER KEY CONNECTOR 3P PLUG HOUSING WITHOUT G.F.

PDF

Japanese

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

Downloaded from Arrow.com.

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Product Specification

5mm Power Key Connector Without GF

PDF

English

Qualification Test Report

5mm Power Key Connector Without GF

PDF

Japanese

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector System Wire-to-Board
Connector & Contact Terminates To Printed Circuit Board
Product Type Connector
Glow Wire Rating Standard Part - Not Glow Wire

Electrical Characteristics

Operating Voltage (VAC) 300

Contact Features

Contact Type Socket
Contact Size 1.5 x .5

Mechanical Attachment

Contact Retention Without

Dimensions

Overall Length 20 mm [.787 in]

Usage Conditions

Operating Temperature Range -30 – 105 °C [-22 – 221 °F]

Downloaded from Arrow.com.

Operation/Application

For Use With Header

Industry Standards

UL Flammability Rating UL 94V-0

Packaging Features

Packaging Quantity 500
Packaging Method Bag

Statement of Compliance

Statement of Compliance
PDF

Downloaded from Arrow.com.