

Part Number : 39036012
Product Description : 2.36mm Diameter Standard .093" Pin and Socket Plug Housing with Positive Latch, UL 94V-2, without Panel Mount, 1 Circuit
Status : Active
Product Category : Connector Housings
Engineering Part Number : 3191-01P1

Documents and Resources

Drawings

039036012_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

SPK-3191-001-001.pdf

PS-3191-001-001.pdf

Part Details

General

Status	Active
Category	Connector Housings
Series	3191
Description	2.36mm Diameter Standard .093" Pin and Socket Plug Housing with Positive Latch, UL 94V-2, without Panel Mount, 1 Circuit
Application	Wire-to-Board, Wire-to-Wire
Comments	Polarized to Mating Part
Component Type	Plug
Product Name	Standard .093"
UPC	800753756854

Downloaded from Arrow.com.

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	1
Color - Resin	Natural
Flammability	94V-2
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1467.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description
2.36mm Diameter Standard .093" Pin and Socket Receptacle Housing with Positive Latch, UL 94V-2, without Panel Mount, 1 Circuit

Use with Part(s)

Description
Standard .093" Pin and Socket Female Crimp Terminals
Standard .093" Pin and Socket Female Crimp Terminals
Standard .093" Pin and Socket Female Crimp Terminal
Standard .093" Pin and Socket Male Crimp Terminals

Downloaded from Arrow.com.

Standard .093" Pin and Socket Male Crimp Terminals
Standard .093" Pin and Socket Male Crimp Terminal
Standard .093" Pin and Socket Male Crimp Grounding Terminals
2.36mm Diameter, Standard .093" Pin and Socket Male Crimp Terminals

This document was generated on Nov 18, 2026

Downloaded from Arrow.com.