Part Number : 1300110280
Product Description : Mini-Change B-Size Double-Ended Cordset, 8 Poles, Male (Straight) to Female (Straight), 22/18 AWG, Yellow PVC Cable, 15.0m (49.21') Length
Series Number : 130011
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 228020A04M150



Documents and Resources

Drawings

1300110280_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	130011
Description	Mini-Change B-Size Double-Ended Cordset, 8 Poles, Male (Straight) to Female (Straight), 22/18 AWG, Yellow PVC Cable, 15.0m (49.21') Length
IP Rating	IP67
Product Name	Mini-Change
Protocol	DeviceNet
Type	Double Ended
UPC	78172514373

Agency

CSA	LR6837

Electrical

Current - Maximum per Contact	2.5A
Voltage - Maximum	300V

Physical

Cable Diameter	7.36mm (.290")
Cable Length	15.0m (49.21')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change
Connector End B	Mini-Change
Coupling Style	Threaded

Downloaded from Arrow.com.

Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	66.660/g
Orientation	Straight to Straight
Poles	8
Temperature Range - Operating	-20° to +90°C
Wire/Cable Type	AWM 2661
Wire Size (AWG)	18, 22

Downloaded from Arrow.com.