This site uses cookies to simplify and improve your usage and experience of this website. Cookies are small text files stored on the device you are using to access this website. If you ignore this message and continue without changing your browser settings, we will assume that you are consenting to our use of cookies. For further information on our use of cookies, please see our Privacy Statement. (http://honeywell.com/Privacy/Pages/en.aspx)

Don't show this message again

8LS1-4C

Distributor Inventory

Input part number for stock availability



Actual product appearance may vary.

Enclosed Switches Series LS: Wobble - Flexible Cable; 1NC 1NO DPDT Snap Action, Double Break; 20 mm [0.79 in] conduit; Compact/Non Plug-in

Narrow Your Search

Modify Your Search

Products

Technology

Industries Served

Sales & Service | Distributor Inventory

Overview | Specs | Documentation | Application Notes

Product Specifications

Availability	Global
Operating Force (OF)	1,39 N [5 oz] max.
Pretravel (PT)	28,6 mm [1.125 in] max.
Product Type	MICRO SWITCH™ Compact Limit Switches
Actuator	Wobble - Flexible Cable
Circuitry	1NC 1NO SPDT Snap Action, Double Break
Ampere Rating	10 A Ind./0.8 A Res./0.4 Res./0.1 A Res.
Supply Voltage	120 Vac, 240 Vac, 480 Vac/115 Vdc/230 Vdc/550 Vdc
Housing Material	Zinc Die-Cast
Termination Type	20 mm [0.79 in] Conduit
Housing Type	Compact / Non Plug-In
Series Name	LS
Sealing	NEMA 1, 3, 4, 6, 13
Operating Temperature	-29 °C to 71 °C [-20 °F to 160 °F]
Comment	Solder terminals, 5.5 in flexible cable actuator with external boot seal
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Sealed	Industrial
Operating Position (OP)	28,58 mm [1.125 in] max. in any direction

Downloaded from Arrow.com.

Product Search

Product Type: All Product Types

Industry: All Industries

Search Term: Start Here ...

New Products Only

Entire Product Catalog

Search

My Links

eCOM Login (/index.php?ci_id=50629&la_id=1)
Request Access to eCOM (/ecom access request)
Rep/AD Portal Login (/index.php?ci_id=50606&la_id=1)
Rep/AD Portal Access Request (/index.php?ci_id=50630&la_id=1)
Sample Request (/samplerequest)
Digital U - HWL Learning Hub Login (/index.php?ci_id=50607&la_id=1)
Digital U - HWL Learning Hub Access Request (/index.php?ci_id=146099&la_id=1)
Limitless Microsite (/index.php?ci_id=50631&la_id=1)
Supplier Microsite (/index.php?ci_id=44887&la_id=1)

Literature and Media

Data Sheets (/white paper and technical data sheets library)
Videos (/videos)
Literature (/literature)
Literature Request (/index.php?ci_id=50636&la_id=1)
White Papers (/whitepapers)
Application Notes (/application notes)
Application Demos (/index.php?ci_id=141383&la_id=1)
CAD Renderings (/cad renderings)

Contacts

Customer Service (/index.php?ci_id=50608&la_id=1)
Technical Support (/index.php?ci_id=50609&la_id=1)
Global Sales & Service (/index.php?ci_id=50610&la_id=1)
Website Feedback (/index.php?ci_id=142628&la_id=1)

(///www.youtube.com/user/SensingAndControl) (///twitter.com/HONSensorSwitch)

Downloaded from Arrow.com.