

Plug Component			Plug Strip Dimension			Wire Spec.	Terminal ROJ & Strip			Terminal Component		
Color	Component	Qty	Strip	ROJ	Color		Strip	ROJ	Color	Component	Color	Qty
40P Black 90±5°A	LT-550(20A 250V) (IEC 320 C20)	1	6±1	25±3	Black	SJT 12AWGX3C 105°C BLACK	5±1	18±3	Black	LT-549(20A 250V) (IEC 320 C19)	40P BK 90±5°A	1
BLACK	(550 Inner Body)	1	6±1	25±3	White	Length: 3048±50 mm	5±1	18±3	White	terminals	Phosphor bronze	3
Nickel-Plated	2*5 Inlet Blades	2	6±1	25±3	Green		5±1	18±3	Green	(549 Inner Body)	BLACK	1
Nickel-Plated	2*6 Inlet Blades	1										

NOTE：

1. PLUG：LT-550 AMERICAN TYPE
2. CONNECTOR：LT-549 IEC-60320 C19
3. CORD：SJT 12AWGX3C 105°C BLACK 10FT
4. APPROVALS：UL, C-UL
5. Supplier for flexible cord： RHYTHM
6. Hi-Pot Test:2000v/1min<1mA>

Marking:

RHYTHM: (UL)E88231 SJT 3X12AWG(3.13mm) 105°c 300V VW-1 CSA LL54496 SJT 3X12AWG(3.13mm)105°c 300V VW-1 RHYTHM R

Modification History

	DESCRIPTION	DATE

DRAWER	Eric	DATE	20/10/17	P/N	800-12-32D-BL-0010F-1
APPROVE		REV.	0	Dr.No.	1091049
		比 例		TOL.	±5mm
				ALL DIMENSIONS IN mm	

CnC Tech

Industrial Cable and Connector Technology

Downloaded from Arrow.com.