



Part Number : 1301100050

Series Number : 130110

Product Category : Lamps and Lights

Product Description : Pro-Yellow 400W Metal Halide High Bay Light with Lamp Molded 18/3 SJTW 1.83m (6.0') Pulse Start

Status : Obsolete

Engineering Number : 8575-MH-PS

Documents & Resources

Product Environment Compliance

Compliance

| | |
|--------------------|--------------|
| China RoHS | Not Reviewed |
| EU ELV | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC | Not Reviewed |
| EU RoHS | Not Reviewed |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

| | |
|----------|------------------|
| Status | Obsolete |
| Category | Lamps and Lights |
| Series | 130110 |

| | |
|--------------------|---|
| Description | Pro-Yellow 400W Metal Halide High Bay Light with Lamp Molded 18/3 SJTW 1.83m (6.0') Pulse Start |
| NEMA Configuration | NEMA 5-15 |
| NEMA Rating | Rain Tight |
| Product Family | Wide-Area Lighting Products |
| Product Name | Pro-Yellow |
| Type | Wide Area Lamps |
| UPC | 78172505741 |

Agency

| | |
|----|---------|
| UL | E174253 |
|----|---------|

Electrical

| | |
|-----------------------------|--------------|
| Lamp Wattage - Maximum | 400W |
| Lumens | 26000 |
| On/Off Switch | No |
| Voltage (Fixture) - Maximum | 120VAC 60 HZ |

Physical

| | |
|-------------------------|-----------------------------|
| Bulb Type | Metal Halide - Pulse Start |
| Cord Length - Primary | 0.91m (3.0') |
| Cord Length - Secondary | N/A |
| Cord Type - Primary | 16/3 SOOW |
| Depth | N/A |
| Duty | General |
| Guard Included | Yes |
| Guard Type | Steel |
| Height | 463.55mm (18.250") |
| Lamp Type | BT37/ED-37 Type O |
| Length | N/A |
| Material - Guard | #10 Gauge Zinc-plated Steel |
| Mounting Style | Hook |
| Net Weight | 6477.293/g |
| Outlet | None |
| Packaging Type | Carton |

This document was generated on May 08, 2024